

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753563

Luminaire Tested: LD4D75BD010-EU4DR6570959030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5420.0 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753563

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753563

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	66	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	58	55		63	58	55		62	58	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	583059
5°	583531
10°	604080
15°	605075
20°	557075
25°	474653
30°	363363
35°	256708
40°	151530
45°	61514
50°	22301
55°	12420
60°	7124
65°	3930
70°	4121
75°	3208
80°	3335
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 61514 cd/sqm



TEST NUMBER: P753563

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	513.8	9.5
10°-20°	1482.2	27.3
20°-30°	1778.4	32.8
30°-40°	1195.1	22.1
40°-50°	357.8	6.6
50°-60°	63.1	1.2
60°-70°	17.9	0.3
70°-80°	8.8	0.2
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3774.4	69.6
0°-40°	4969.5	91.7
0°-60°	5390.4	99.5
0°-90°	5420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5336	
5°	5320	514
15°	5349	1482
25°	3937	1778
35°	1925	1195
45°	398	358
55°	65	63
65°	15	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P753563

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5336.4
2.5°	5359.1
5°	5320.4
7.5°	5400.8
10°	5444.8
12.5°	5434.2
15°	5349.2
17.5°	5141.5
20°	4791.1
22.5°	4378.6
25°	3937.2
27.5°	3439.0
30°	2880.1
32.5°	2373.6
35°	1924.6
37.5°	1481.0
40°	1062.4
42.5°	693.9
45°	398.1
47.5°	210.8
50°	131.2
52.5°	91.0
55°	65.2
57.5°	47.0
60°	32.6
62.5°	21.2
65°	15.2
67.5°	13.6
70°	12.9
72.5°	9.9
75°	7.6
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)