

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753565

Luminaire Tested: LD4D75BD010-EU4DR6570959030-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P753565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6612.6 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753565

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P753565

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93						93													
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85						85													
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78						78													
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72						72													
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66						66													
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61						61													
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56						56													
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52						52													
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49						49													
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46						46													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350657
5°	349774
10°	349472
15°	338702
20°	308343
25°	268702
30°	223486
35°	177083
40°	127810
45°	80745
50°	42086
55°	22371
60°	11751
65°	6468
70°	2715
75°	2979
80°	2085
85°	1742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 80745 cd/sqm



TEST NUMBER: P753565

CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	567.8	8.6
10°-20°	1554.8	23.5
20°-30°	1900.5	28.7
30°-40°	1542.0	23.3
40°-50°	768.4	11.6
50°-60°	214.3	3.2
60°-70°	48.7	0.7
70°-80°	12.7	0.2
80°-90°	3.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4023.1	60.8
0°-40°	5565.2	84.2
0°-60°	6547.9	99.0
0°-90°	6612.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6612.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6004	
5°	5966	568
15°	5602	1555
25°	4170	1901
35°	2484	1542
45°	978	768
55°	220	214
65°	47	49
75°	13	13
85°	3	3
90°	0	



TEST NUMBER: P753565
CATALOG NUMBER: LD4D75BD010-EU4DR6570959030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6004.0
2.5°	5999.6
5°	5966.1
7.5°	5946.7
10°	5892.8
12.5°	5783.4
15°	5601.7
17.5°	5317.6
20°	4961.1
22.5°	4576.5
25°	4169.7
27.5°	3734.8
30°	3313.9
32.5°	2898.3
35°	2483.7
37.5°	2069.9
40°	1676.4
42.5°	1307.6
45°	977.6
47.5°	681.1
50°	463.2
52.5°	319.4
55°	219.7
57.5°	148.2
60°	100.6
62.5°	69.7
65°	46.8
67.5°	23.8
70°	15.9
72.5°	15.0
75°	13.2
77.5°	8.8
80°	6.2
82.5°	4.4
85°	2.6
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)