

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752913

Luminaire Tested: LD4D75BD010-EU4DR2570959024-4LBDP1MW

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P752913  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR2570959024-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4860.7 lumens  
Efficiency: N/A  
Efficacy: 67.1 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P752913

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P752913

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  |  | 99  | 97  | 96  |  | 97  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  |  | 96  | 93  | 91  |  | 94  |
| 4   | 103 | 97  | 93  | 90  | 102 | 96  | 93  | 90  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 91  |
| 5   | 100 | 93  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 81  |  | 87  | 83  | 81  |  | 85  |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  |  | 84  | 80  | 78  |  | 83  |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  |  | 81  | 78  | 75  |  | 80  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 80  | 76  | 73  |  | 79  | 75  | 73  |  | 78  |
| 10  | 85  | 78  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 71  |  | 76  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2014309 |
| 5°  | 1876077 |
| 10° | 1338256 |
| 15° | 788186  |
| 20° | 490416  |
| 25° | 269141  |
| 30° | 123085  |
| 35° | 46617   |
| 40° | 21109   |
| 45° | 12686   |
| 50° | 5269    |
| 55° | 3391    |
| 60° | 2360    |
| 65° | 1603    |
| 70° | 256     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12686 cd/sqm



TEST NUMBER: P752913

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1470.1 | 30.2      |
| 10°-20°   | 1991.1 | 41.0      |
| 20°-30°   | 1053.7 | 21.7      |
| 30°-40°   | 260.1  | 5.4       |
| 40°-50°   | 63.4   | 1.3       |
| 50°-60°   | 16.7   | 0.3       |
| 60°-70°   | 5.6    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 4514.8 | 92.9      |
| 0°-40°    | 4774.9 | 98.2      |
| 0°-60°    | 4855.0 | 99.9      |
| 0°-90°    | 4860.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4860.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 18436 |      |
| 5°  | 17105 | ###  |
| 15° | 6968  | 1991 |
| 25° | 2232  | 1054 |
| 35° | 350   | 260  |
| 45° | 82    | 63   |
| 55° | 18    | 17   |
| 65° | 6     | 6    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P752913

CATALOG NUMBER: LD4D75BD010-EU4DR2570959024-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 18435.8 |
| 2.5°  | 18132.8 |
| 5°    | 17105.3 |
| 7.5°  | 15040.9 |
| 10°   | 12062.2 |
| 12.5° | 9118.3  |
| 15°   | 6968.0  |
| 17.5° | 5430.5  |
| 20°   | 4217.8  |
| 22.5° | 3163.2  |
| 25°   | 2232.5  |
| 27.5° | 1497.1  |
| 30°   | 975.6   |
| 32.5° | 593.6   |
| 35°   | 349.5   |
| 37.5° | 213.9   |
| 40°   | 148.0   |
| 42.5° | 113.1   |
| 45°   | 82.1    |
| 47.5° | 49.6    |
| 50°   | 31.0    |
| 52.5° | 22.5    |
| 55°   | 17.8    |
| 57.5° | 13.9    |
| 60°   | 10.8    |
| 62.5° | 8.5     |
| 65°   | 6.2     |
| 67.5° | 2.3     |
| 70°   | 0.8     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)