

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753185

Luminaire Tested: LD4D75BD010-EU4DR4070959035-4LBDP1LI

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P753185  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR4070959035-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7941.1 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P753185

CATALOG NUMBER: LD4D75BD010-EU4DR4070959035-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P753185

CATALOG NUMBER: LD4D75BD010-EU4DR4070959035-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 |  | 103 | 101 | 100 |  | 99  |
| 2   | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99  | 102 | 99  | 97  |  | 99  | 97  | 95  |  | 96  |
| 3   | 106 | 101 | 97  | 94  | 104 | 100 | 96  | 93  | 97  | 94  | 92  |  | 95  | 93  | 90  |  | 93  |
| 4   | 102 | 97  | 92  | 89  | 101 | 95  | 91  | 88  | 93  | 90  | 87  |  | 92  | 89  | 86  |  | 90  |
| 5   | 99  | 92  | 88  | 84  | 97  | 91  | 87  | 84  | 90  | 86  | 83  |  | 88  | 85  | 83  |  | 87  |
| 6   | 95  | 88  | 84  | 80  | 94  | 88  | 83  | 80  | 86  | 82  | 80  |  | 85  | 82  | 79  |  | 84  |
| 7   | 92  | 85  | 80  | 77  | 91  | 84  | 80  | 77  | 83  | 79  | 76  |  | 82  | 79  | 76  |  | 81  |
| 8   | 89  | 82  | 77  | 74  | 88  | 81  | 77  | 74  | 80  | 76  | 73  |  | 79  | 76  | 73  |  | 78  |
| 9   | 86  | 79  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  |  | 76  | 73  | 70  |  | 76  |
| 10  | 83  | 76  | 71  | 68  | 82  | 75  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 68  |  | 73  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2020111 |
| 5°  | 2010290 |
| 10° | 1900166 |
| 15° | 1615385 |
| 20° | 1100999 |
| 25° | 459378  |
| 30° | 144445  |
| 35° | 67132   |
| 40° | 37127   |
| 45° | 17028   |
| 50° | 8261    |
| 55° | 4534    |
| 60° | 2360    |
| 65° | 827     |
| 70° | 351     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17028 cd/sqm



TEST NUMBER: P753185

CATALOG NUMBER: LD4D75BD010-EU4DR4070959035-4LBDP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1711.5 | 21.6      |
| 10°-20°   | 3834.2 | 48.3      |
| 20°-30°   | 1919.3 | 24.2      |
| 30°-40°   | 351.8  | 4.4       |
| 40°-50°   | 97.1   | 1.2       |
| 50°-60°   | 22.8   | 0.3       |
| 60°-70°   | 4.4    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 7464.9 | 94.0      |
| 0°-40°    | 7816.7 | 98.4      |
| 0°-60°    | 7936.6 | 99.9      |
| 0°-90°    | 7941.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 7941.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 18489 |      |
| 5°  | 18329 | ###  |
| 15° | 14281 | 3834 |
| 25° | 3810  | 1919 |
| 35° | 503   | 352  |
| 45° | 110   | 97   |
| 55° | 24    | 23   |
| 65° | 3     | 4    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P753185

CATALOG NUMBER: LD4D75BD010-EU4DR4070959035-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 18488.9 |
| 2.5°  | 18461.9 |
| 5°    | 18329.0 |
| 7.5°  | 17905.6 |
| 10°   | 17126.9 |
| 12.5° | 15912.9 |
| 15°   | 14280.9 |
| 17.5° | 12158.5 |
| 20°   | 9469.1  |
| 22.5° | 6455.7  |
| 25°   | 3810.5  |
| 27.5° | 2014.4  |
| 30°   | 1144.9  |
| 32.5° | 739.9   |
| 35°   | 503.3   |
| 37.5° | 359.7   |
| 40°   | 260.3   |
| 42.5° | 178.2   |
| 45°   | 110.2   |
| 47.5° | 70.2    |
| 50°   | 48.6    |
| 52.5° | 34.6    |
| 55°   | 23.8    |
| 57.5° | 15.1    |
| 60°   | 10.8    |
| 62.5° | 6.5     |
| 65°   | 3.2     |
| 67.5° | 2.2     |
| 70°   | 1.1     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)