

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753340

Luminaire Tested: LD4D75BD010-EU4DR5070959035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR5070959035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7515.3 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753340

CATALOG NUMBER: LD4D75BD010-EU4DR5070959035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P753340

CATALOG NUMBER: LD4D75BD010-EU4DR5070959035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	82	82	80
5	96	89	84	80	95	88	83	79	86	82	79	85	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	74	74	74	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	63	63	62
10	78	70	64	61	77	69	64	61	68	64	61	68	64	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1323038
5°	1309173
10°	1287609
15°	1172471
20°	975634
25°	692558
30°	366568
35°	149375
40°	55483
45°	25403
50°	10420
55°	5448
60°	2688
65°	801
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25403 cd/sqm



TEST NUMBER: P753340

CATALOG NUMBER: LD4D75BD010-EU4DR5070959035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1128.2	15.0
10°-20°	2851.3	37.9
20°-30°	2561.2	34.1
30°-40°	801.9	10.7
40°-50°	140.4	1.9
50°-60°	28.0	0.4
60°-70°	4.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6540.7	87.0
0°-40°	7342.6	97.7
0°-60°	7511.1	99.9
0°-90°	7515.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7515.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12109	
5°	11936	###
15°	10365	2851
25°	5745	2561
35°	1120	802
45°	164	140
55°	29	28
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753340

CATALOG NUMBER: LD4D75BD010-EU4DR5070959035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12109.0
2.5°	12048.8
5°	11936.5
7.5°	11765.0
10°	11605.7
12.5°	11095.2
15°	10365.3
17.5°	9438.3
20°	8390.9
22.5°	7179.0
25°	5744.7
27.5°	4223.5
30°	2905.5
32.5°	1891.7
35°	1119.9
37.5°	643.2
40°	389.0
42.5°	253.2
45°	164.4
47.5°	100.0
50°	61.3
52.5°	41.9
55°	28.6
57.5°	19.4
60°	12.3
62.5°	7.1
65°	3.1
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)