

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753461

Luminaire Tested: LD4D75BD010-EU4DR6070959024-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753461
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6070959024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6484.8 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753461

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P753461

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	709059
5°	707325
10°	730814
15°	731572
20°	673127
25°	572532
30°	436248
35°	308501
40°	181154
45°	73102
50°	24409
55°	11753
60°	4829
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 73102 cd/sqm



TEST NUMBER: P753461

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	622.1	9.6
10°-20°	1791.7	27.6
20°-30°	2144.5	33.1
30°-40°	1434.3	22.1
40°-50°	425.3	6.6
50°-60°	61.2	0.9
60°-70°	5.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4558.3	70.3
0°-40°	5992.6	92.4
0°-60°	6479.0	99.9
0°-90°	6484.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6484.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6490	
5°	6449	622
15°	6468	1792
25°	4749	2144
35°	2313	1434
45°	473	425
55°	62	61
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753461

CATALOG NUMBER: LD4D75BD010-EU4DR6070959024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6489.6
2.5°	6481.3
5°	6449.1
7.5°	6536.5
10°	6587.1
12.5°	6577.9
15°	6467.5
17.5°	6207.0
20°	5789.2
22.5°	5287.6
25°	4749.1
27.5°	4142.6
30°	3457.8
32.5°	2846.7
35°	2312.9
37.5°	1778.2
40°	1270.1
42.5°	837.5
45°	473.1
47.5°	242.1
50°	143.6
52.5°	93.0
55°	61.7
57.5°	39.6
60°	22.1
62.5°	9.2
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)