

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753540

Luminaire Tested: LD4D75BD010-EU4DR6570959024-4LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P753540  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR6570959024-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5949.6 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P753540  
CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P753540

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	315498
5°	314704
10°	314434
15°	304739
20°	277428
25°	241759
30°	201076
35°	159322
40°	114994
45°	72651
50°	37871
55°	20131
60°	10571
65°	5818
70°	2442
75°	2685
80°	1883
85°	1608

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 72651 cd/sqm



TEST NUMBER: P753540

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	510.9	8.6
10°-20°	1398.9	23.5
20°-30°	1710.0	28.7
30°-40°	1387.4	23.3
40°-50°	691.4	11.6
50°-60°	192.9	3.2
60°-70°	43.8	0.7
70°-80°	11.4	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3619.7	60.8
0°-40°	5007.2	84.2
0°-60°	5891.4	99.0
0°-90°	5949.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5949.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5402	
5°	5368	511
15°	5040	1399
25°	3752	1710
35°	2235	1387
45°	880	691
55°	198	193
65°	42	44
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P753540

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5402.0
2.5°	5398.0
5°	5367.9
7.5°	5350.4
10°	5302.0
12.5°	5203.6
15°	5040.0
17.5°	4784.4
20°	4463.7
22.5°	4117.6
25°	3751.6
27.5°	3360.3
30°	2981.6
32.5°	2607.7
35°	2234.6
37.5°	1862.3
40°	1508.3
42.5°	1176.5
45°	879.6
47.5°	612.8
50°	416.8
52.5°	287.4
55°	197.7
57.5°	133.4
60°	90.5
62.5°	62.7
65°	42.1
67.5°	21.4
70°	14.3
72.5°	13.5
75°	11.9
77.5°	7.9
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)