

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753082

Luminaire Tested: LD4D75BD010-EU4DR3570959027-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753082
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR3570959027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6232.9 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753082

CATALOG NUMBER: LD4D75BD010-EU4DR3570959027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753082

CATALOG NUMBER: LD4D75BD010-EU4DR3570959027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1873800
5°	1829771
10°	1649105
15°	1279976
20°	725985
25°	282438
30°	105372
35°	57755
40°	37754
45°	22977
50°	14618
55°	10325
60°	7561
65°	4111
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22977 cd/sqm



TEST NUMBER: P753082

CATALOG NUMBER: LD4D75BD010-EU4DR3570959027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1534.3	24.6
10°-20°	2995.7	48.1
20°-30°	1221.8	19.6
30°-40°	292.4	4.7
40°-50°	121.8	2.0
50°-60°	50.4	0.8
60°-70°	15.8	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5751.8	92.3
0°-40°	6044.2	97.0
0°-60°	6216.5	99.7
0°-90°	6232.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6232.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17150	
5°	16683	###
15°	11316	2996
25°	2343	1222
35°	433	292
45°	149	122
55°	54	50
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753082

CATALOG NUMBER: LD4D75BD010-EU4DR3570959027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	17149.8
2.5°	17046.9
5°	16683.1
7.5°	15957.3
10°	14864.0
12.5°	13324.6
15°	11315.7
17.5°	8858.7
20°	6243.8
22.5°	3981.4
25°	2342.8
27.5°	1324.3
30°	835.2
32.5°	586.4
35°	433.0
37.5°	334.8
40°	264.7
42.5°	203.9
45°	148.7
47.5°	111.3
50°	86.0
52.5°	68.3
55°	54.2
57.5°	44.0
60°	34.6
62.5°	25.3
65°	15.9
67.5°	5.6
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)