

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753551

Luminaire Tested: LD4D75BD010-EU4DR6570959027-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P753551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5959.4 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753551

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P753551

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	316023
5°	315225
10°	314956
15°	305247
20°	277888
25°	242165
30°	201413
35°	159586
40°	115185
45°	72767
50°	37934
55°	20161
60°	10583
65°	5818
70°	2442
75°	2685
80°	1883
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 72767 cd/sqm

TEST NUMBER: P753551

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	511.7	8.6
10°-20°	1401.3	23.5
20°-30°	1712.8	28.7
30°-40°	1389.7	23.3
40°-50°	692.5	11.6
50°-60°	193.2	3.2
60°-70°	43.9	0.7
70°-80°	11.4	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3625.8	60.8
0°-40°	5015.5	84.2
0°-60°	5901.2	99.0
0°-90°	5959.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5959.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5411	
5°	5377	512
15°	5048	1401
25°	3758	1713
35°	2238	1390
45°	881	693
55°	198	193
65°	42	44
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P753551

CATALOG NUMBER: LD4D75BD010-EU4DR6570959027-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5411.0
2.5°	5407.0
5°	5376.8
7.5°	5359.3
10°	5310.8
12.5°	5212.2
15°	5048.4
17.5°	4792.4
20°	4471.1
22.5°	4124.4
25°	3757.9
27.5°	3365.9
30°	2986.6
32.5°	2612.1
35°	2238.3
37.5°	1865.4
40°	1510.8
42.5°	1178.4
45°	881.0
47.5°	613.9
50°	417.5
52.5°	287.8
55°	198.0
57.5°	133.6
60°	90.6
62.5°	62.8
65°	42.1
67.5°	21.5
70°	14.3
72.5°	13.5
75°	11.9
77.5°	8.0
80°	5.6
82.5°	4.0
85°	2.4
87.5°	1.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)