

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752977

Luminaire Tested: LD4D75BD010-EU4DR2570959050-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR2570959050-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7165.4 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752977

CATALOG NUMBER: LD4D75BD010-EU4DR2570959050-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P752977

CATALOG NUMBER: LD4D75BD010-EU4DR2570959050-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2969347
5°	2765577
10°	1972758
15°	1161884
20°	722938
25°	396749
30°	181448
35°	68719
40°	31122
45°	18712
50°	7768
55°	5010
60°	3496
65°	2353
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18712 cd/sqm

TEST NUMBER: P752977

CATALOG NUMBER: LD4D75BD010-EU4DR2570959050-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2167.1	30.2
10°-20°	2935.1	41.0
20°-30°	1553.2	21.7
30°-40°	383.4	5.4
40°-50°	93.6	1.3
50°-60°	24.6	0.3
60°-70°	8.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6655.4	92.9
0°-40°	7038.8	98.2
0°-60°	7157.0	99.9
0°-90°	7165.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7165.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27177	
5°	25215	###
15°	10272	2935
25°	3291	1553
35°	515	383
45°	121	94
55°	26	25
65°	9	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752977

CATALOG NUMBER: LD4D75BD010-EU4DR2570959050-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	27176.7
2.5°	26730.1
5°	25215.4
7.5°	22172.2
10°	17781.2
12.5°	13441.6
15°	10271.7
17.5°	8005.3
20°	6217.6
22.5°	4662.9
25°	3291.0
27.5°	2206.9
30°	1438.2
32.5°	875.0
35°	515.2
37.5°	315.3
40°	218.2
42.5°	166.8
45°	121.1
47.5°	73.1
50°	45.7
52.5°	33.1
55°	26.3
57.5°	20.6
60°	16.0
62.5°	12.6
65°	9.1
67.5°	3.4
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)