

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753095

Luminaire Tested: LD4D75BD010-EU4DR3570959030-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR3570959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6421.3 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753095

CATALOG NUMBER: LD4D75BD010-EU4DR3570959030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753095

CATALOG NUMBER: LD4D75BD010-EU4DR3570959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89	101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85	98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81	94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78	91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74	88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72	86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69	83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1930430
5°	1885071
10°	1698943
15°	1318650
20°	747925
25°	290974
30°	108551
35°	59502
40°	38895
45°	23672
50°	15060
55°	10648
60°	7801
65°	4240
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23672 cd/sqm



TEST NUMBER: P753095

CATALOG NUMBER: LD4D75BD010-EU4DR3570959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1580.7	24.6
10°-20°	3086.3	48.1
20°-30°	1258.7	19.6
30°-40°	301.2	4.7
40°-50°	125.5	2.0
50°-60°	52.0	0.8
60°-70°	16.3	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5925.7	92.3
0°-40°	6226.9	97.0
0°-60°	6404.4	99.7
0°-90°	6421.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6421.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17668	
5°	17187	###
15°	11658	3086
25°	2414	1259
35°	446	301
45°	153	126
55°	56	52
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753095

CATALOG NUMBER: LD4D75BD010-EU4DR3570959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	17668.1
2.5°	17562.1
5°	17187.3
7.5°	16439.6
10°	15313.2
12.5°	13727.3
15°	11657.6
17.5°	9126.5
20°	6432.5
22.5°	4101.7
25°	2413.6
27.5°	1364.3
30°	860.4
32.5°	604.1
35°	446.1
37.5°	344.9
40°	272.7
42.5°	210.0
45°	153.2
47.5°	114.7
50°	88.6
52.5°	70.3
55°	55.9
57.5°	45.3
60°	35.7
62.5°	26.0
65°	16.4
67.5°	5.8
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)