

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753173

Luminaire Tested: LD4D75BD010-EU4DR4070959030-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR4070959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7100.5 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753173

CATALOG NUMBER: LD4D75BD010-EU4DR4070959030-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P753173

CATALOG NUMBER: LD4D75BD010-EU4DR4070959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1806288
5°	1797515
10°	1699042
15°	1444400
20°	984459
25°	410758
30°	129154
35°	60022
40°	33190
45°	15220
50°	7394
55°	4038
60°	2120
65°	750
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15220 cd/sqm



TEST NUMBER: P753173

CATALOG NUMBER: LD4D75BD010-EU4DR4070959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1530.3	21.6
10°-20°	3428.3	48.3
20°-30°	1716.1	24.2
30°-40°	314.6	4.4
40°-50°	86.8	1.2
50°-60°	20.4	0.3
60°-70°	3.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6674.7	94.0
0°-40°	6989.3	98.4
0°-60°	7096.5	99.9
0°-90°	7100.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7100.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16532	
5°	16389	###
15°	12769	3428
25°	3407	1716
35°	450	315
45°	98	87
55°	21	20
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753173

CATALOG NUMBER: LD4D75BD010-EU4DR4070959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	16531.9
2.5°	16507.7
5°	16389.0
7.5°	16010.4
10°	15314.1
12.5°	14228.6
15°	12769.3
17.5°	10871.6
20°	8466.8
22.5°	5772.4
25°	3407.2
27.5°	1801.1
30°	1023.7
32.5°	661.5
35°	450.0
37.5°	321.6
40°	232.7
42.5°	159.4
45°	98.5
47.5°	62.8
50°	43.5
52.5°	30.9
55°	21.2
57.5°	13.5
60°	9.7
62.5°	5.8
65°	2.9
67.5°	1.9
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)