

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753446

Luminaire Tested: LD4D75BD010-EU4DR5570959050-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753446
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR5570959050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7149.6 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753446

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P753446

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	875954
5°	841165
10°	837988
15°	813919
20°	729798
25°	603141
30°	455601
35°	330349
40°	211406
45°	96558
50°	31582
55°	13620
60°	5856
65°	776
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 96558 cd/sqm



TEST NUMBER: P753446

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	729.8	10.2
10°-20°	1991.7	27.9
20°-30°	2269.7	31.7
30°-40°	1545.2	21.6
40°-50°	532.5	7.4
50°-60°	73.6	1.0
60°-70°	7.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4991.2	69.8
0°-40°	6536.4	91.4
0°-60°	7142.4	99.9
0°-90°	7149.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7149.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8017	
5°	7669	730
15°	7196	1992
25°	5003	2270
35°	2477	1545
45°	625	532
55°	72	74
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753446

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8017.1
2.5°	7833.3
5°	7669.4
7.5°	7588.9
10°	7553.1
12.5°	7433.9
15°	7195.5
17.5°	6817.0
20°	6276.6
22.5°	5652.7
25°	5003.0
27.5°	4326.4
30°	3611.2
32.5°	3005.2
35°	2476.7
37.5°	1974.0
40°	1482.2
42.5°	1027.2
45°	624.9
47.5°	336.8
50°	185.8
52.5°	110.3
55°	71.5
57.5°	45.7
60°	26.8
62.5°	11.9
65°	3.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)