

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753641

Luminaire Tested: LD4D75BD010-EU4DR7070959030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR7070959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5652.5 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P753641
CATALOG NUMBER: LD4D75BD010-EU4DR7070959030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753641
 CATALOG NUMBER: LD4D75BD010-EU4DR7070959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	694352
5°	673720
10°	654938
15°	646339
20°	603549
25°	453423
30°	320531
35°	113535
40°	59705
45°	63584
50°	65850
55°	67091
60°	67501
65°	66081
70°	62358
75°	57750
80°	51280
85°	41620

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 67513 cd/sqm



TEST NUMBER: P753641

CATALOG NUMBER: LD4D75BD010-EU4DR7070959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	579.4	10.3
10°-20°	1589.2	28.1
20°-30°	1750.3	31.0
30°-40°	668.8	11.8
40°-50°	315.8	5.6
50°-60°	313.9	5.6
60°-70°	251.3	4.4
70°-80°	144.5	2.6
80°-90°	39.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3918.9	69.3
0°-40°	4587.7	81.2
0°-60°	5217.4	92.3
0°-90°	5652.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5652.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6355	
5°	6143	579
15°	5714	1589
25°	3761	1750
35°	851	669
45°	412	316
55°	352	314
65°	256	251
75°	137	144
85°	33	39
90°	0	



TEST NUMBER: P753641

CATALOG NUMBER: LD4D75BD010-EU4DR7070959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6355.0
2.5°	6288.6
5°	6142.7
7.5°	6020.9
10°	5903.2
12.5°	5803.6
15°	5714.0
17.5°	5497.7
20°	5190.8
22.5°	4528.8
25°	3761.1
27.5°	3274.1
30°	2540.6
32.5°	1641.1
35°	851.2
37.5°	459.8
40°	418.6
42.5°	415.5
45°	411.5
47.5°	402.5
50°	387.4
52.5°	370.3
55°	352.2
57.5°	332.0
60°	308.9
62.5°	282.7
65°	255.6
67.5°	225.4
70°	195.2
72.5°	165.0
75°	136.8
77.5°	107.7
80°	81.5
82.5°	57.4
85°	33.2
87.5°	13.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)