

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752951

Luminaire Tested: LD4D75BD010-EU4DR2570959035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR2570959035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6796.8 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752951

CATALOG NUMBER: LD4D75BD010-EU4DR2570959035-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P752951

CATALOG NUMBER: LD4D75BD010-EU4DR2570959035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2816611
5°	2623314
10°	1871286
15°	1102114
20°	685754
25°	376339
30°	172112
35°	65184
40°	29524
45°	17754
50°	7360
55°	4743
60°	3322
65°	2249
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17754 cd/sqm



TEST NUMBER: P752951

CATALOG NUMBER: LD4D75BD010-EU4DR2570959035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2055.6	30.2
10°-20°	2784.1	41.0
20°-30°	1473.3	21.7
30°-40°	363.7	5.4
40°-50°	88.7	1.3
50°-60°	23.3	0.3
60°-70°	7.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6313.1	92.9
0°-40°	6676.8	98.2
0°-60°	6788.8	99.9
0°-90°	6796.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6796.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25779	
5°	23918	###
15°	9743	2784
25°	3122	1473
35°	489	364
45°	115	89
55°	25	23
65°	9	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752951

CATALOG NUMBER: LD4D75BD010-EU4DR2570959035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	25778.8
2.5°	25355.1
5°	23918.3
7.5°	21031.7
10°	16866.6
12.5°	12750.1
15°	9743.3
17.5°	7593.5
20°	5897.8
22.5°	4423.1
25°	3121.7
27.5°	2093.4
30°	1364.2
32.5°	830.0
35°	488.7
37.5°	299.1
40°	207.0
42.5°	158.2
45°	114.9
47.5°	69.3
50°	43.3
52.5°	31.4
55°	24.9
57.5°	19.5
60°	15.2
62.5°	11.9
65°	8.7
67.5°	3.3
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)