

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753263

Luminaire Tested: LD4D75BD010-EU4DR4570959035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR4570959035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7791.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753263

CATALOG NUMBER: LD4D75BD010-EU4DR4570959035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P753263

CATALOG NUMBER: LD4D75BD010-EU4DR4570959035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			98
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	91		103	98	94	91		95	92	89			93	90	88			91
4	100	94	89	85		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	83	80		86	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	77	75			80
7	89	81	75	72		87	80	75	72		79	74	71			78	74	71			77
8	85	77	72	68		84	76	71	68		75	71	68			74	70	67			73
9	82	73	68	65		81	73	68	65		72	68	65			71	67	64			71
10	79	70	65	62		78	70	65	62		69	65	62			68	64	61			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1504608
5°	1461768
10°	1398511
15°	1279931
20°	1015434
25°	633943
30°	349410
35°	156898
40°	61787
45°	29127
50°	13802
55°	7220
60°	3540
65°	827
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29127 cd/sqm



TEST NUMBER: P753263

CATALOG NUMBER: LD4D75BD010-EU4DR4570959035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1252.3	16.1
10°-20°	3082.0	39.6
20°-30°	2440.6	31.3
30°-40°	812.7	10.4
40°-50°	161.3	2.1
50°-60°	36.6	0.5
60°-70°	5.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6774.9	87.0
0°-40°	7587.6	97.4
0°-60°	7785.6	99.9
0°-90°	7791.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7791.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13771	
5°	13328	###
15°	11315	3082
25°	5258	2441
35°	1176	813
45°	188	161
55°	38	37
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753263

CATALOG NUMBER: LD4D75BD010-EU4DR4570959035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13770.8
2.5°	13680.9
5°	13327.8
7.5°	13036.4
10°	12605.3
12.5°	12031.3
15°	11315.3
17.5°	10238.7
20°	8733.2
22.5°	6939.5
25°	5258.5
27.5°	3850.5
30°	2769.5
32.5°	1883.5
35°	1176.3
37.5°	697.5
40°	433.2
42.5°	284.9
45°	188.5
47.5°	121.3
50°	81.2
52.5°	54.2
55°	37.9
57.5°	24.9
60°	16.2
62.5°	8.7
65°	3.2
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)