

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753417

Luminaire Tested: LD4D75BD010-EU4DR5570959035-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR5570959035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5841.1 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753417

CATALOG NUMBER: LD4D75BD010-EU4DR5570959035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P753417

CATALOG NUMBER: LD4D75BD010-EU4DR5570959035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	715647
5°	687221
10°	684638
15°	664969
20°	596236
25°	492760
30°	372220
35°	269887
40°	172725
45°	78881
50°	25803
55°	11125
60°	4786
65°	620
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 78881 cd/sqm



TEST NUMBER: P753417

CATALOG NUMBER: LD4D75BD010-EU4DR5570959035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	596.2	10.2
10°-20°	1627.2	27.9
20°-30°	1854.4	31.7
30°-40°	1262.4	21.6
40°-50°	435.0	7.4
50°-60°	60.1	1.0
60°-70°	5.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4077.8	69.8
0°-40°	5340.2	91.4
0°-60°	5835.3	99.9
0°-90°	5841.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5841.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6550	
5°	6266	596
15°	5879	1627
25°	4087	1854
35°	2023	1262
45°	510	435
55°	58	60
65°	2	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753417

CATALOG NUMBER: LD4D75BD010-EU4DR5570959035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6549.9
2.5°	6399.8
5°	6265.8
7.5°	6200.1
10°	6170.9
12.5°	6073.5
15°	5878.7
17.5°	5569.5
20°	5127.9
22.5°	4618.2
25°	4087.4
27.5°	3534.7
30°	2950.3
32.5°	2455.2
35°	2023.4
37.5°	1612.7
40°	1211.0
42.5°	839.2
45°	510.5
47.5°	275.1
50°	151.8
52.5°	90.1
55°	58.4
57.5°	37.3
60°	21.9
62.5°	9.7
65°	2.4
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)