

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753578

Luminaire Tested: LD4D75BD010-EU4DR6570959035-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P753578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6682.2 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P753578
CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P753578
 CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 93 | | | | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 94 | 91 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 90 | 86 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 78 | | | | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 77 | 74 | 80 | 76 | 73 | 72 | | | | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 74 | 70 | 88 | 80 | 74 | 69 | 78 | 73 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 66 | | | | | | | | | | | | | | | | | | | |
| 6 | 85 | 75 | 69 | 64 | 83 | 74 | 68 | 64 | 73 | 67 | 63 | 71 | 67 | 63 | 70 | 66 | 62 | 61 | | | | | | | | | | | | | | | | | | | |
| 7 | 80 | 70 | 64 | 59 | 79 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 61 | 58 | 56 | | | | | | | | | | | | | | | | | | | |
| 8 | 76 | 66 | 59 | 55 | 75 | 65 | 59 | 55 | 64 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 52 | | | | | | | | | | | | | | | | | | | |
| 9 | 72 | 61 | 55 | 51 | 71 | 61 | 55 | 51 | 60 | 54 | 51 | 59 | 54 | 50 | 58 | 54 | 50 | 49 | | | | | | | | | | | | | | | | | | | |
| 10 | 68 | 58 | 52 | 47 | 67 | 57 | 51 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 46 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 354354 |
| 5° | 353456 |
| 10° | 353154 |
| 15° | 342269 |
| 20° | 311593 |
| 25° | 271531 |
| 30° | 225840 |
| 35° | 178944 |
| 40° | 129152 |
| 45° | 81596 |
| 50° | 42532 |
| 55° | 22605 |
| 60° | 11868 |
| 65° | 6537 |
| 70° | 2732 |
| 75° | 3024 |
| 80° | 2085 |
| 85° | 1809 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 81596 cd/sqm



TEST NUMBER: P753578

CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBS1H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 573.8 | 8.6 |
| 10°-20° | 1571.2 | 23.5 |
| 20°-30° | 1920.5 | 28.7 |
| 30°-40° | 1558.3 | 23.3 |
| 40°-50° | 776.5 | 11.6 |
| 50°-60° | 216.6 | 3.2 |
| 60°-70° | 49.2 | 0.7 |
| 70°-80° | 12.8 | 0.2 |
| 80°-90° | 3.3 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4065.5 | 60.8 |
| 0°-40° | 5623.8 | 84.2 |
| 0°-60° | 6616.9 | 99.0 |
| 0°-90° | 6682.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6682.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6067 | |
| 5° | 6029 | 574 |
| 15° | 5661 | 1571 |
| 25° | 4214 | 1921 |
| 35° | 2510 | 1558 |
| 45° | 988 | 777 |
| 55° | 222 | 217 |
| 65° | 47 | 49 |
| 75° | 13 | 13 |
| 85° | 3 | 3 |
| 90° | 0 | |



TEST NUMBER: P753578

CATALOG NUMBER: LD4D75BD010-EU4DR6570959035-4LBS1H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 6067.3 |
| 2.5° | 6062.8 |
| 5° | 6028.9 |
| 7.5° | 6009.3 |
| 10° | 5954.9 |
| 12.5° | 5844.4 |
| 15° | 5660.7 |
| 17.5° | 5373.6 |
| 20° | 5013.4 |
| 22.5° | 4624.7 |
| 25° | 4213.6 |
| 27.5° | 3774.1 |
| 30° | 3348.8 |
| 32.5° | 2928.9 |
| 35° | 2509.8 |
| 37.5° | 2091.7 |
| 40° | 1694.0 |
| 42.5° | 1321.3 |
| 45° | 987.9 |
| 47.5° | 688.3 |
| 50° | 468.1 |
| 52.5° | 322.8 |
| 55° | 222.0 |
| 57.5° | 149.8 |
| 60° | 101.6 |
| 62.5° | 70.4 |
| 65° | 47.3 |
| 67.5° | 24.1 |
| 70° | 16.0 |
| 72.5° | 15.2 |
| 75° | 13.4 |
| 77.5° | 8.9 |
| 80° | 6.2 |
| 82.5° | 4.5 |
| 85° | 2.7 |
| 87.5° | 1.8 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)