

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741580

Luminaire Tested: LD4D08D010-EU4DR600210IC9030-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P741580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR600210IC9030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 590.3 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741580

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P741580

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	76603
5°	78486
10°	79438
15°	75674
20°	66717
25°	53961
30°	36499
35°	18287
40°	2967
45°	2905
50°	2958
55°	3010
60°	3103
65°	3154
70°	3227
75°	3251
80°	3146
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 3251 cd/sqm



TEST NUMBER: P741580

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	11.6
10°-20°	185.0	31.3
20°-30°	199.1	33.7
30°-40°	86.5	14.7
40°-50°	14.5	2.5
50°-60°	14.1	2.4
60°-70°	12.1	2.0
70°-80°	8.1	1.4
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	452.5	76.7
0°-40°	539.1	91.3
0°-60°	567.7	96.2
0°-90°	590.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	590.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	701	
5°	716	68
15°	669	185
25°	448	199
35°	137	87
45°	19	15
55°	16	14
65°	12	12
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P741580

CATALOG NUMBER: LD4D08D010-EU4DR600210IC9030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	701.1
2.5°	720.8
5°	715.6
7.5°	717.2
10°	716.0
12.5°	701.2
15°	669.0
17.5°	625.7
20°	573.8
22.5°	518.2
25°	447.6
27.5°	358.0
30°	289.3
32.5°	223.0
35°	137.1
37.5°	58.7
40°	20.8
42.5°	19.1
45°	18.8
47.5°	18.2
50°	17.4
52.5°	16.6
55°	15.8
57.5°	15.0
60°	14.2
62.5°	13.2
65°	12.2
67.5°	11.2
70°	10.1
72.5°	8.9
75°	7.7
77.5°	6.4
80°	5.0
82.5°	3.6
85°	2.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)