

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753353

Luminaire Tested: LD4D75BD010-EU4DR5070959040-4LBDP1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P753353  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D75BD010-EU4DR5070959040-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7866.6 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P753353

CATALOG NUMBER: LD4D75BD010-EU4DR5070959040-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P753353

CATALOG NUMBER: LD4D75BD010-EU4DR5070959040-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 102 |  | 102 | 101 | 99  |  | 98  | 97  | 97  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 98  | 95  |  | 97  | 95  | 93  |  | 95  | 93  | 91  |
| 3   | 105 | 99  | 95  | 91  |  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 88  | 86  |
| 4   | 100 | 94  | 89  | 85  |  | 99  | 93  | 88  | 85  |  | 90  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  |  | 95  | 88  | 83  | 79  |  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 77  |
| 6   | 92  | 84  | 79  | 75  |  | 91  | 83  | 79  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 74  |
| 7   | 88  | 80  | 75  | 71  |  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 8   | 85  | 76  | 71  | 67  |  | 84  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 66  |
| 9   | 81  | 73  | 68  | 64  |  | 80  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 71  | 67  | 64  |  | 70  | 66  | 63  |
| 10  | 78  | 70  | 64  | 61  |  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 63  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1384891 |
| 5°  | 1370373 |
| 10° | 1347809 |
| 15° | 1227287 |
| 20° | 1021236 |
| 25° | 724927  |
| 30° | 383701  |
| 35° | 156365  |
| 40° | 58079   |
| 45° | 26593   |
| 50° | 10896   |
| 55° | 5696    |
| 60° | 2797    |
| 65° | 827     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26593 cd/sqm



TEST NUMBER: P753353

CATALOG NUMBER: LD4D75BD010-EU4DR5070959040-4LBDP1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1181.0 | 15.0      |
| 10°-20°   | 2984.6 | 37.9      |
| 20°-30°   | 2681.0 | 34.1      |
| 30°-40°   | 839.4  | 10.7      |
| 40°-50°   | 147.0  | 1.9       |
| 50°-60°   | 29.3   | 0.4       |
| 60°-70°   | 4.4    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 6846.5 | 87.0      |
| 0°-40°    | 7685.9 | 97.7      |
| 0°-60°    | 7862.2 | 99.9      |
| 0°-90°    | 7866.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 7866.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 12675 |      |
| 5°  | 12494 | ###  |
| 15° | 10850 | 2985 |
| 25° | 6013  | 2681 |
| 35° | 1172  | 839  |
| 45° | 172   | 147  |
| 55° | 30    | 29   |
| 65° | 3     | 4    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P753353

CATALOG NUMBER: LD4D75BD010-EU4DR5070959040-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 12675.1 |
| 2.5°  | 12612.1 |
| 5°    | 12494.5 |
| 7.5°  | 12315.0 |
| 10°   | 12148.3 |
| 12.5° | 11614.0 |
| 15°   | 10849.9 |
| 17.5° | 9879.6  |
| 20°   | 8783.1  |
| 22.5° | 7514.7  |
| 25°   | 6013.2  |
| 27.5° | 4421.0  |
| 30°   | 3041.3  |
| 32.5° | 1980.2  |
| 35°   | 1172.3  |
| 37.5° | 673.2   |
| 40°   | 407.2   |
| 42.5° | 265.0   |
| 45°   | 172.1   |
| 47.5° | 104.7   |
| 50°   | 64.1    |
| 52.5° | 43.8    |
| 55°   | 29.9    |
| 57.5° | 20.3    |
| 60°   | 12.8    |
| 62.5° | 7.5     |
| 65°   | 3.2     |
| 67.5° | 1.1     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)