

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741203

Luminaire Tested: LD4D08D010-EU4DR350210IC9035-4LBDP1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P741203  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D08D010-EU4DR350210IC9035-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 652.5 lumens  
Efficiency: N/A  
Efficacy: 73.3 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P741203  
CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P741203

CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0										
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100							100												
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96							96												
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92							92												
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88							88												
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84							84												
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81							81												
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78							78												
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75							75												
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72							72												
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70							70												
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68							68												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	196145
5°	191542
10°	172621
15°	133985
20°	75996
25°	29560
30°	11027
35°	6042
40°	3951
45°	2410
50°	1530
55°	1086
60°	787
65°	440
70°	32
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2410 cd/sqm



TEST NUMBER: P741203

CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.6	24.6
10°-20°	313.6	48.1
20°-30°	127.9	19.6
30°-40°	30.6	4.7
40°-50°	12.7	2.0
50°-60°	5.3	0.8
60°-70°	1.7	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	602.1	92.3
0°-40°	632.7	97.0
0°-60°	650.7	99.7
0°-90°	652.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	652.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1795	
5°	1746	161
15°	1184	314
25°	245	128
35°	45	31
45°	16	13
55°	6	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P741203

CATALOG NUMBER: LD4D08D010-EU4DR350210IC9035-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1795.2
2.5°	1784.4
5°	1746.4
7.5°	1670.4
10°	1555.9
12.5°	1394.8
15°	1184.5
17.5°	927.3
20°	653.6
22.5°	416.8
25°	245.2
27.5°	138.7
30°	87.4
32.5°	61.4
35°	45.3
37.5°	35.1
40°	27.7
42.5°	21.3
45°	15.6
47.5°	11.6
50°	9.0
52.5°	7.2
55°	5.7
57.5°	4.6
60°	3.6
62.5°	2.6
65°	1.7
67.5°	0.6
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)