

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740987

Luminaire Tested: LD4D08D010-EU4DR200210IC9040-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR200210IC9040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 904.6 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740987
CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P740987
 CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94	92	91	91	89	88																		
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	92	91	91	89	88	86	85	85	83																		
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	89	88	86	85	83	81	81	79	77																		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	83	81	79	77	75	73	71	69																		
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	83	81	79	77	75	73	71	69	67	65																		
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	81	79	77	75	73	71	69	67	65	63																		
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	79	77	75	73	71	69	67	65	63	61																		
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	77	75	73	71	69	67	65	63	61	59																		
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	75	73	71	69	67	65	63	61	59	57																		
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	73	71	69	67	65	63	61	59	57	55																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	562551
5°	507535
10°	284855
15°	144799
20°	61311
25°	28294
30°	14976
35°	8070
40°	4322
45°	2550
50°	1479
55°	781
60°	503
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2550 cd/sqm



TEST NUMBER: P740987

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.6	40.5
10°-20°	361.0	39.9
20°-30°	117.9	13.0
30°-40°	40.2	4.4
40°-50°	13.5	1.5
50°-60°	4.1	0.4
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	845.5	93.5
0°-40°	885.6	97.9
0°-60°	903.2	99.8
0°-90°	904.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	904.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5149	
5°	4628	367
15°	1280	361
25°	235	118
35°	60	40
45°	16	13
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740987

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5148.7
0.5°	5148.7
1°	5142.3
1.5°	5129.5
2°	5106.1
2.5°	5074.9
3°	5030.9
3.5°	4969.5
4°	4878.2
4.5°	4767.3
5°	4627.5
5.5°	4443.6
6°	4255.2
6.5°	4039.2
7°	3827.9
7.5°	3580.3
8°	3359.3
8.5°	3136.9
9°	2931.5
9.5°	2743.1
10°	2567.5
12.5°	1843.6
15°	1280.1
17.5°	836.3
20°	527.3
22.5°	341.6
25°	234.7
27.5°	165.1
30°	118.7
32.5°	85.3
35°	60.5
37.5°	42.2
40°	30.3
42.5°	22.0
45°	16.5
47.5°	12.8
50°	8.7
52.5°	5.5
55°	4.1
57.5°	3.2
60°	2.3
62.5°	1.8
65°	1.4



TEST NUMBER: P740987
CATALOG NUMBER: LD4D08D010-EU4DR200210IC9040-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.9
70°		0.5

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)