

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753590

Luminaire Tested: LD4D75BD010-EU4DR6570959040-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P753590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6494.3 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753590

CATALOG NUMBER: LD4D75BD010-EU4DR6570959040-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P753590

CATALOG NUMBER: LD4D75BD010-EU4DR6570959040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344384
5°	343513
10°	343221
15°	332643
20°	302830
25°	263895
30°	219487
35°	173910
40°	125523
45°	79300
50°	41332
55°	21974
60°	11541
65°	6343
70°	2664
75°	2934
80°	2052
85°	1742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 79300 cd/sqm



TEST NUMBER: P753590

CATALOG NUMBER: LD4D75BD010-EU4DR6570959040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	557.6	8.6
10°-20°	1527.0	23.5
20°-30°	1866.5	28.7
30°-40°	1514.4	23.3
40°-50°	754.7	11.6
50°-60°	210.5	3.2
60°-70°	47.8	0.7
70°-80°	12.5	0.2
80°-90°	3.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3951.2	60.8
0°-40°	5465.6	84.2
0°-60°	6430.8	99.0
0°-90°	6494.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6494.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5897	
5°	5859	558
15°	5502	1527
25°	4095	1867
35°	2439	1514
45°	960	755
55°	216	211
65°	46	48
75°	13	12
85°	3	3
90°	0	



TEST NUMBER: P753590

CATALOG NUMBER: LD4D75BD010-EU4DR6570959040-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5896.6
2.5°	5892.2
5°	5859.3
7.5°	5840.3
10°	5787.4
12.5°	5680.0
15°	5501.5
17.5°	5222.4
20°	4872.4
22.5°	4494.6
25°	4095.1
27.5°	3667.9
30°	3254.6
32.5°	2846.5
35°	2439.2
37.5°	2032.8
40°	1646.4
42.5°	1284.2
45°	960.1
47.5°	668.9
50°	454.9
52.5°	313.7
55°	215.8
57.5°	145.6
60°	98.8
62.5°	68.5
65°	45.9
67.5°	23.4
70°	15.6
72.5°	14.7
75°	13.0
77.5°	8.7
80°	6.1
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)