

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754393

Luminaire Tested: LD4D80BD010-EU4DR7070959024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR7070959024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6582.7 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P754393
CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P754393

CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	808628
5°	784593
10°	762733
15°	752724
20°	702881
25°	528047
30°	373280
35°	132222
40°	69532
45°	74060
50°	76678
55°	78120
60°	78602
65°	76939
70°	72613
75°	67291
80°	59712
85°	48515

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 78636 cd/sqm



TEST NUMBER: P754393

CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	674.7	10.3
10°-20°	1850.8	28.1
20°-30°	2038.4	31.0
30°-40°	778.8	11.8
40°-50°	367.7	5.6
50°-60°	365.6	5.6
60°-70°	292.7	4.4
70°-80°	168.2	2.6
80°-90°	45.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4563.9	69.3
0°-40°	5342.7	81.2
0°-60°	6076.1	92.3
0°-90°	6582.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6582.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7401	
5°	7154	675
15°	6654	1851
25°	4380	2038
35°	991	779
45°	479	368
55°	410	366
65°	298	293
75°	159	168
85°	39	46
90°	0	



TEST NUMBER: P754393

CATALOG NUMBER: LD4D80BD010-EU4DR7070959024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7400.9
2.5°	7323.5
5°	7153.6
7.5°	7011.9
10°	6874.8
12.5°	6758.8
15°	6654.5
17.5°	6402.5
20°	6045.1
22.5°	5274.1
25°	4380.1
27.5°	3812.9
30°	2958.7
32.5°	1911.2
35°	991.3
37.5°	535.5
40°	487.5
42.5°	483.9
45°	479.3
47.5°	468.7
50°	451.1
52.5°	431.2
55°	410.1
57.5°	386.7
60°	359.7
62.5°	329.3
65°	297.6
67.5°	262.5
70°	227.3
72.5°	192.2
75°	159.4
77.5°	125.4
80°	94.9
82.5°	66.8
85°	38.7
87.5°	15.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)