

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754252

Luminaire Tested: LD4D80BD010-EU4DR6070959027-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754252  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR6070959027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6708.9 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P754252

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P754252  
 CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	870557
5°	891968
10°	902737
15°	859980
20°	758239
25°	613280
30°	414838
35°	207877
40°	33718
45°	33005
50°	33673
55°	34174
60°	35116
65°	35910
70°	36770
75°	37192
80°	35865
85°	29836

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 37192 cd/sqm



TEST NUMBER: P754252

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	777.3	11.6
10°-20°	2103.0	31.3
20°-30°	2262.6	33.7
30°-40°	983.5	14.7
40°-50°	165.2	2.5
50°-60°	160.6	2.4
60°-70°	137.4	2.0
70°-80°	91.9	1.4
80°-90°	27.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5142.8	76.7
0°-40°	6126.3	91.3
0°-60°	6452.1	96.2
0°-90°	6708.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6708.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7968	
5°	8133	777
15°	7603	2103
25°	5087	2263
35°	1558	983
45°	214	165
55°	179	161
65°	139	137
75°	88	92
85°	24	27
90°	0	



TEST NUMBER: P754252

CATALOG NUMBER: LD4D80BD010-EU4DR6070959027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7967.7
2.5°	8191.7
5°	8132.6
7.5°	8151.3
10°	8136.7
12.5°	7968.8
15°	7602.7
17.5°	7111.2
20°	6521.2
22.5°	5889.7
25°	5087.1
27.5°	4068.9
30°	3288.1
32.5°	2534.2
35°	1558.5
37.5°	666.7
40°	236.4
42.5°	217.8
45°	213.6
47.5°	206.3
50°	198.1
52.5°	188.7
55°	179.4
57.5°	170.1
60°	160.7
62.5°	150.4
65°	138.9
67.5°	127.5
70°	115.1
72.5°	101.6
75°	88.1
77.5°	72.6
80°	57.0
82.5°	40.4
85°	23.8
87.5°	8.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)