

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753209

Luminaire Tested: LD4D75BD010-EU4DR4070959050-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR4070959050-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7105.6 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753209

CATALOG NUMBER: LD4D75BD010-EU4DR4070959050-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P753209

CATALOG NUMBER: LD4D75BD010-EU4DR4070959050-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	97
2	110	106	103	100		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		104	100	96	93		97	94	92		95	93	90		93	91	89
4	102	97	92	89		101	95	91	88		93	90	87		92	89	86		90	87	85
5	99	92	88	84		97	91	87	84		90	86	83		88	85	83		87	84	82
6	95	88	84	80		94	88	83	80		86	82	80		85	82	79		84	81	79
7	92	85	80	77		91	84	80	77		83	79	76		82	79	76		81	78	76
8	89	82	77	74		88	81	77	74		80	76	73		79	76	73		78	75	73
9	86	79	74	71		85	78	74	71		77	73	71		76	73	70		76	72	70
10	83	76	71	68		82	75	71	68		75	71	68		74	70	68		73	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1807577
5°	1798787
10°	1700252
15°	1445429
20°	985168
25°	411047
30°	129242
35°	60076
40°	33218
45°	15235
50°	7394
55°	4057
60°	2120
65°	750
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15235 cd/sqm

TEST NUMBER: P753209

CATALOG NUMBER: LD4D75BD010-EU4DR4070959050-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1531.4	21.6
10°-20°	3430.8	48.3
20°-30°	1717.3	24.2
30°-40°	314.8	4.4
40°-50°	86.9	1.2
50°-60°	20.4	0.3
60°-70°	3.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6679.5	94.0
0°-40°	6994.3	98.4
0°-60°	7101.6	99.9
0°-90°	7105.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7105.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16544	
5°	16401	###
15°	12778	3431
25°	3410	1717
35°	450	315
45°	99	87
55°	21	20
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753209

CATALOG NUMBER: LD4D75BD010-EU4DR4070959050-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	16543.7
2.5°	16519.5
5°	16400.6
7.5°	16021.8
10°	15325.0
12.5°	14238.7
15°	12778.4
17.5°	10879.3
20°	8472.9
22.5°	5776.5
25°	3409.6
27.5°	1802.4
30°	1024.4
32.5°	662.0
35°	450.4
37.5°	321.8
40°	232.9
42.5°	159.5
45°	98.6
47.5°	62.8
50°	43.5
52.5°	30.9
55°	21.3
57.5°	13.5
60°	9.7
62.5°	5.8
65°	2.9
67.5°	1.9
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)