

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754407

Luminaire Tested: LD4D80BD010-EU4DR7070959027-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754407  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR7070959027-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7829.6 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P754407  
CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P754407

CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	961790
5°	933218
10°	907208
15°	895294
20°	836025
25°	628060
30°	443982
35°	157272
40°	82697
45°	88075
50°	91211
55°	92921
60°	93505
65°	91521
70°	86381
75°	79998
80°	71038
85°	57667

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 93521 cd/sqm



TEST NUMBER: P754407

CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	802.5	10.3
10°-20°	2201.4	28.1
20°-30°	2424.5	31.0
30°-40°	926.3	11.8
40°-50°	437.4	5.6
50°-60°	434.8	5.6
60°-70°	348.1	4.4
70°-80°	200.1	2.6
80°-90°	54.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5428.4	69.3
0°-40°	6354.7	81.2
0°-60°	7227.0	92.3
0°-90°	7829.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7829.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8803	
5°	8509	803
15°	7915	2201
25°	5210	2424
35°	1179	926
45°	570	437
55°	488	435
65°	354	348
75°	190	200
85°	46	54
90°	0	



TEST NUMBER: P754407

CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8802.7
2.5°	8710.8
5°	8508.7
7.5°	8340.0
10°	8177.0
12.5°	8039.0
15°	7914.9
17.5°	7615.3
20°	7190.2
22.5°	6273.1
25°	5209.7
27.5°	4535.2
30°	3519.1
32.5°	2273.2
35°	1179.1
37.5°	636.9
40°	579.8
42.5°	575.6
45°	570.0
47.5°	557.5
50°	536.6
52.5°	512.9
55°	487.8
57.5°	459.9
60°	427.9
62.5°	391.6
65°	354.0
67.5°	312.2
70°	270.4
72.5°	228.6
75°	189.5
77.5°	149.1
80°	112.9
82.5°	79.4
85°	46.0
87.5°	18.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)