

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753449

Luminaire Tested: LD4D75BD010-EU4DR5570959050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR5570959050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8631.9 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753449

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P753449

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1057568
5°	1015564
10°	1011741
15°	982676
20°	881104
25°	728194
30°	550060
35°	398841
40°	255236
45°	116568
50°	38126
55°	16458
60°	7080
65°	931
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 116568 cd/sqm



TEST NUMBER: P753449

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	881.1	10.2
10°-20°	2404.7	27.9
20°-30°	2740.3	31.7
30°-40°	1865.5	21.6
40°-50°	642.8	7.4
50°-60°	88.9	1.0
60°-70°	8.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6026.1	69.8
0°-40°	7891.6	91.4
0°-60°	8623.3	99.9
0°-90°	8631.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8631.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9679	
5°	9260	881
15°	8687	2405
25°	6040	2740
35°	2990	1865
45°	754	643
55°	86	89
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753449

CATALOG NUMBER: LD4D75BD010-EU4DR5570959050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	9679.3
2.5°	9457.4
5°	9259.5
7.5°	9162.4
10°	9119.2
12.5°	8975.3
15°	8687.4
17.5°	8230.4
20°	7577.9
22.5°	6824.7
25°	6040.3
27.5°	5223.5
30°	4359.9
32.5°	3628.2
35°	2990.2
37.5°	2383.2
40°	1789.5
42.5°	1240.2
45°	754.4
47.5°	406.6
50°	224.3
52.5°	133.1
55°	86.4
57.5°	55.2
60°	32.4
62.5°	14.4
65°	3.6
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)