

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754355

Luminaire Tested: LD4D80BD010-EU4DR6570959035-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6570959035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7075.9 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P754355

CATALOG NUMBER: LD4D80BD010-EU4DR6570959035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P754355

CATALOG NUMBER: LD4D80BD010-EU4DR6570959035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	761187
5°	761813
10°	788639
15°	789939
20°	727275
25°	619669
30°	474387
35°	335138
40°	197828
45°	80318
50°	29117
55°	16211
60°	9309
65°	5119
70°	5367
75°	4179
80°	4342
85°	3761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 80318 cd/sqm



TEST NUMBER: P754355

CATALOG NUMBER: LD4D80BD010-EU4DR6570959035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	670.8	9.5
10°-20°	1935.1	27.3
20°-30°	2321.7	32.8
30°-40°	1560.2	22.1
40°-50°	467.1	6.6
50°-60°	82.4	1.2
60°-70°	23.4	0.3
70°-80°	11.5	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4927.6	69.6
0°-40°	6487.8	91.7
0°-60°	7037.3	99.5
0°-90°	7075.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7075.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6967	
5°	6946	671
15°	6984	1935
25°	5140	2322
35°	2513	1560
45°	520	467
55°	85	82
65°	20	23
75°	10	11
85°	3	4
90°	0	



TEST NUMBER: P754355

CATALOG NUMBER: LD4D80BD010-EU4DR6570959035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6966.7
2.5°	6996.4
5°	6945.9
7.5°	7050.8
10°	7108.3
12.5°	7094.4
15°	6983.5
17.5°	6712.3
20°	6254.9
22.5°	5716.3
25°	5140.1
27.5°	4489.7
30°	3760.1
32.5°	3098.7
35°	2512.6
37.5°	1933.5
40°	1387.0
42.5°	905.9
45°	519.8
47.5°	275.2
50°	171.3
52.5°	118.8
55°	85.1
57.5°	61.4
60°	42.6
62.5°	27.7
65°	19.8
67.5°	17.8
70°	16.8
72.5°	12.9
75°	9.9
77.5°	8.9
80°	6.9
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)