

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740852

Luminaire Tested: LD4D08D010-EU4DR150210IC9024-4LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P740852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR150210IC9024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 615.6 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P740852

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P740852

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	943649	943649	943649
5°	554528	547353	551682
10°	165500	166657	169213
15°	41170	41969	40675
20°	12314	14262	12576
25°	4339	5531	4394
30°	1595	2097	1625
35°	799	900	777
40°	504	554	504
45°	371	399	371
50°	299	299	299
55°	251	251	251
60°	197	197	197
65°	150	150	150
70°	132	132	132
75°	83	83	106
80°	55	55	55
85°	33	33	33

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 399 cd/sqm



TEST NUMBER: P740852

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	399.2	64.9
10°-20°	164.2	26.7
20°-30°	32.6	5.3
30°-40°	8.1	1.3
40°-50°	4.3	0.7
50°-60°	3.2	0.5
60°-70°	2.2	0.4
70°-80°	1.3	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.0	96.8
0°-40°	604.2	98.2
0°-60°	611.6	99.4
0°-90°	615.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	8386	8386	8386	8386	8386	
5°	5456	5400	5386	5423	5428	398
15°	474	483	483	475	468	162
25°	56	63	71	63	56	29
35°	11	12	12	12	11	7
45°	5	5	6	5	5	4
55°	4	4	4	4	4	3
65°	2	2	2	2	2	2
75°	1	1	1	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P740852

CATALOG NUMBER: LD4D08D010-EU4DR150210IC9024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	8386.5	8386.5	8386.5	8386.5	8386.5
2.5°	7564.9	7571.3	7573.8	7581.3	7609.0
5°	5456.4	5400.3	5385.8	5423.0	5428.4
7.5°	3232.2	3243.5	3285.1	3294.3	3260.9
10°	1773.7	1788.3	1786.1	1798.9	1813.5
12.5°	907.1	895.7	892.2	906.7	886.5
15°	474.0	482.8	483.2	474.7	468.3
17.5°	254.9	265.2	282.2	268.4	247.1
20°	150.5	159.8	174.3	163.0	153.7
22.5°	93.0	100.5	110.8	101.9	94.4
25°	55.7	63.2	71.0	62.8	56.4
27.5°	33.0	39.4	44.4	39.1	32.7
30°	21.3	24.9	28.0	24.5	21.7
32.5°	14.9	16.3	17.8	16.3	14.9
35°	11.0	11.7	12.4	11.7	10.7
37.5°	8.5	9.2	9.6	8.9	8.2
40°	7.1	7.5	7.8	7.5	7.1
42.5°	6.0	6.4	6.4	6.4	6.0
45°	5.3	5.3	5.7	5.3	5.3
47.5°	4.6	4.6	5.0	4.6	4.6
50°	4.3	4.3	4.3	4.3	4.3
52.5°	3.9	3.9	3.9	3.9	3.9
55°	3.6	3.6	3.6	3.6	3.6
57.5°	3.2	3.2	3.2	3.2	3.2
60°	2.8	2.8	2.8	2.8	2.8
62.5°	2.5	2.5	2.5	2.5	2.5
65°	2.1	2.1	2.1	2.1	2.1
67.5°	2.1	2.1	2.1	2.1	2.1
70°	1.8	1.8	1.8	1.8	1.8
72.5°	1.4	1.4	1.4	1.4	1.4
75°	1.1	1.1	1.1	1.1	1.4
77.5°	1.1	1.1	1.1	1.1	1.1
80°	0.7	0.7	0.7	0.7	0.7
82.5°	0.7	0.7	0.7	0.7	0.7
85°	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)