

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741649

Luminaire Tested: LD4D08D010-EU4DR650210IC9027-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P741649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR650210IC9027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 620.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741649
CATALOG NUMBER: LD4D08D010-EU4DR650210IC9027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P741649

CATALOG NUMBER: LD4D08D010-EU4DR650210IC9027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93						93													
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85						85													
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78						78													
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72						72													
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66						66													
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61						61													
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56						56													
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52						52													
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49						49													
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46						46													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32876
5°	32796
10°	32766
15°	31756
20°	28913
25°	25190
30°	20953
35°	16598
40°	11985
45°	7574
50°	3943
55°	2098
60°	1110
65°	608
70°	256
75°	293
80°	202
85°	134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7574 cd/sqm



TEST NUMBER: P741649

CATALOG NUMBER: LD4D08D010-EU4DR650210IC9027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	8.6
10°-20°	145.8	23.5
20°-30°	178.2	28.7
30°-40°	144.6	23.3
40°-50°	72.1	11.6
50°-60°	20.1	3.2
60°-70°	4.6	0.7
70°-80°	1.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	377.2	60.8
0°-40°	521.8	84.2
0°-60°	614.0	99.0
0°-90°	620.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	620.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	563	
5°	559	53
15°	525	146
25°	391	178
35°	233	145
45°	92	72
55°	21	20
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P741649
CATALOG NUMBER: LD4D08D010-EU4DR650210IC9027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	562.9
2.5°	562.5
5°	559.4
7.5°	557.5
10°	552.5
12.5°	542.2
15°	525.2
17.5°	498.6
20°	465.2
22.5°	429.1
25°	390.9
27.5°	350.2
30°	310.7
32.5°	271.8
35°	232.8
37.5°	194.1
40°	157.2
42.5°	122.6
45°	91.7
47.5°	63.9
50°	43.4
52.5°	30.0
55°	20.6
57.5°	13.9
60°	9.5
62.5°	6.5
65°	4.4
67.5°	2.2
70°	1.5
72.5°	1.4
75°	1.3
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)