

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754371

Luminaire Tested: LD4D80BD010-EU4DR6570959040-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754371  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR6570959040-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7425.2 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P754371

CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P754371  
 CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	393753
5°	392760
10°	392426
15°	380325
20°	346243
25°	301728
30°	250954
35°	198843
40°	143516
45°	90665
50°	47256
55°	25120
60°	13188
65°	7255
70°	3040
75°	3362
80°	2321
85°	2010

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 90665 cd/sqm



TEST NUMBER: P754371

CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	637.6	8.6
10°-20°	1745.9	23.5
20°-30°	2134.1	28.7
30°-40°	1731.6	23.3
40°-50°	862.9	11.6
50°-60°	240.6	3.2
60°-70°	54.7	0.7
70°-80°	14.2	0.2
80°-90°	3.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4517.6	60.8
0°-40°	6249.1	84.2
0°-60°	7352.6	99.0
0°-90°	7425.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7425.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6742	
5°	6699	638
15°	6290	1746
25°	4682	2134
35°	2789	1732
45°	1098	863
55°	247	241
65°	52	55
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P754371

CATALOG NUMBER: LD4D80BD010-EU4DR6570959040-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6741.9
2.5°	6737.0
5°	6699.3
7.5°	6677.5
10°	6617.1
12.5°	6494.2
15°	6290.1
17.5°	5971.1
20°	5570.9
22.5°	5138.9
25°	4682.2
27.5°	4193.8
30°	3721.2
32.5°	3254.5
35°	2788.9
37.5°	2324.3
40°	1882.4
42.5°	1468.3
45°	1097.7
47.5°	764.8
50°	520.1
52.5°	358.6
55°	246.7
57.5°	166.4
60°	112.9
62.5°	78.3
65°	52.5
67.5°	26.7
70°	17.8
72.5°	16.8
75°	14.9
77.5°	9.9
80°	6.9
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)