

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P740971

Luminaire Tested: LD4D08D010-EU4DR200210IC9035-4LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P740971  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D08D010-EU4DR200210IC9035-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 878.0 lumens  
Efficiency: N/A  
Efficacy: 98.7 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P740971

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P740971

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	546052
5°	492641
10°	276500
15°	140545
20°	59508
25°	27475
30°	14547
35°	7830
40°	4193
45°	2472
50°	1445
55°	762
60°	481
65°	336
70°	128
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2472 cd/sqm



TEST NUMBER: P740971

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	355.8	40.5
10°-20°	350.4	39.9
20°-30°	114.5	13.0
30°-40°	39.0	4.4
40°-50°	13.1	1.5
50°-60°	3.9	0.4
60°-70°	1.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	820.7	93.5
0°-40°	859.6	97.9
0°-60°	876.7	99.8
0°-90°	878.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	878.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4998	
5°	4492	356
15°	1242	350
25°	228	114
35°	59	39
45°	16	13
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P740971

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4997.7
0.5°	4997.7
1°	4991.5
1.5°	4979.0
2°	4956.3
2.5°	4926.0
3°	4883.3
3.5°	4823.7
4°	4735.1
4.5°	4627.4
5°	4491.7
5.5°	4313.2
6°	4130.3
6.5°	3920.7
7°	3715.6
7.5°	3475.2
8°	3260.7
8.5°	3044.9
9°	2845.5
9.5°	2662.6
10°	2492.2
12.5°	1789.5
15°	1242.5
17.5°	811.7
20°	511.8
22.5°	331.5
25°	227.9
27.5°	160.2
30°	115.3
32.5°	82.8
35°	58.7
37.5°	40.9
40°	29.4
42.5°	21.4
45°	16.0
47.5°	12.5
50°	8.5
52.5°	5.3
55°	4.0
57.5°	3.1
60°	2.2
62.5°	1.8
65°	1.3



TEST NUMBER: P740971

CATALOG NUMBER: LD4D08D010-EU4DR200210IC9035-4LBDP1LI

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.9
70°		0.4

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)