

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741132

Luminaire Tested: LD4D08D010-EU4DR300210IC9035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P741132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR300210IC9035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 771.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741132
CATALOG NUMBER: LD4D08D010-EU4DR300210IC9035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P741132

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	189782	189782	189782
5°	184337	184122	184344
10°	159661	158534	159622
15°	104174	103611	103088
20°	51798	53745	51733
25°	26089	29425	25556
30°	10447	11384	9104
35°	4850	4644	3897
40°	2088	2328	1968
45°	1472	1829	1494
50°	500	1334	536
55°	294	547	307
60°	199	245	199
65°	127	127	127
70°	67	45	67
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1829 cd/sqm



TEST NUMBER: P741132

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.0	28.3
10°-20°	351.1	45.5
20°-30°	151.7	19.7
30°-40°	34.6	4.5
40°-50°	11.9	1.5
50°-60°	2.9	0.4
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.9	93.5
0°-40°	755.5	98.0
0°-60°	770.2	99.9
0°-90°	771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2479	2479	2479	2479	2479	
5°	2399	2397	2396	2401	2399	218
15°	1315	1299	1308	1303	1301	352
25°	309	321	348	312	303	148
35°	52	53	50	49	42	35
45°	14	17	17	17	14	10
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P741132

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2479.4	2479.4	2479.4	2479.4	2479.4
2.5°	2462.9	2461.3	2462.3	2463.5	2463.9
5°	2399.1	2396.8	2396.3	2401.2	2399.2
7.5°	2270.1	2266.9	2261.8	2273.2	2283.8
10°	2054.2	2050.5	2039.7	2045.0	2053.7
12.5°	1735.4	1723.6	1723.3	1740.4	1738.0
15°	1314.6	1298.7	1307.5	1303.2	1300.9
17.5°	884.0	877.9	889.6	886.1	870.8
20°	635.9	637.5	659.8	648.6	635.1
22.5°	464.0	469.8	496.2	467.3	456.8
25°	308.9	320.6	348.4	312.5	302.6
27.5°	190.0	195.4	223.5	187.6	182.3
30°	118.2	115.5	128.8	110.5	103.0
32.5°	77.5	74.1	78.4	70.4	64.3
35°	51.9	52.9	49.7	49.3	41.7
37.5°	32.4	37.2	32.9	35.1	26.8
40°	20.9	27.0	23.3	25.7	19.7
42.5°	17.2	20.8	19.1	20.3	17.5
45°	13.6	16.9	16.9	16.9	13.8
47.5°	7.6	11.3	14.5	11.6	8.0
50°	4.2	5.7	11.2	6.0	4.5
52.5°	2.9	3.3	7.7	3.4	3.0
55°	2.2	2.3	4.1	2.4	2.3
57.5°	1.7	1.8	2.2	1.8	1.7
60°	1.3	1.3	1.6	1.4	1.3
62.5°	1.0	1.0	1.1	1.0	1.0
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.3	0.5	0.5	0.5	0.5
70°	0.3	0.2	0.2	0.2	0.3
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)