

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754379

Luminaire Tested: LD4D80BD010-EU4DR6570959050-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754379  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR6570959050-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5292.0 lumens  
Efficiency: N/A  
Efficacy: 67.1 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P754379

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P754379

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	569281
5°	569756
10°	589813
15°	590789
20°	543924
25°	463453
30°	354784
35°	250653
40°	147950
45°	60061
50°	21774
55°	12134
60°	6949
65°	3826
70°	4025
75°	3124
80°	3272
85°	2758

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 60061 cd/sqm



TEST NUMBER: P754379

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	501.7	9.5
10°-20°	1447.2	27.3
20°-30°	1736.4	32.8
30°-40°	1166.9	22.1
40°-50°	349.3	6.6
50°-60°	61.7	1.2
60°-70°	17.5	0.3
70°-80°	8.6	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3685.3	69.6
0°-40°	4852.2	91.7
0°-60°	5263.1	99.5
0°-90°	5292.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5292.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5210	
5°	5195	502
15°	5223	1447
25°	3844	1736
35°	1879	1167
45°	389	349
55°	64	62
65°	15	18
75°	7	9
85°	2	3
90°	0	



TEST NUMBER: P754379

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5210.3
2.5°	5232.5
5°	5194.8
7.5°	5273.3
10°	5316.2
12.5°	5305.8
15°	5222.9
17.5°	5020.0
20°	4678.0
22.5°	4275.2
25°	3844.3
27.5°	3357.8
30°	2812.1
32.5°	2317.5
35°	1879.2
37.5°	1446.0
40°	1037.3
42.5°	677.5
45°	388.7
47.5°	205.8
50°	128.1
52.5°	88.9
55°	63.7
57.5°	45.9
60°	31.8
62.5°	20.7
65°	14.8
67.5°	13.3
70°	12.6
72.5°	9.6
75°	7.4
77.5°	6.7
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)