

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754380

Luminaire Tested: LD4D80BD010-EU4DR6570959050-4LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754380  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR6570959050-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7104.4 lumens  
Efficiency: N/A  
Efficacy: 90.0 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P754380  
CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P754380  
 CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	764246
5°	764884
10°	791812
15°	793118
20°	730205
25°	622165
30°	476292
35°	336498
40°	198626
45°	80628
50°	29236
55°	16287
60°	9331
65°	5145
70°	5399
75°	4179
80°	4404
85°	3761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 80628 cd/sqm



TEST NUMBER: P754380

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	673.5	9.5
10°-20°	1942.8	27.3
20°-30°	2331.0	32.8
30°-40°	1566.5	22.1
40°-50°	468.9	6.6
50°-60°	82.8	1.2
60°-70°	23.5	0.3
70°-80°	11.5	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4947.4	69.6
0°-40°	6514.0	91.7
0°-60°	7065.7	99.5
0°-90°	7104.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7104.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6995	
5°	6974	674
15°	7012	1943
25°	5161	2331
35°	2523	1567
45°	522	469
55°	86	83
65°	20	24
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P754380

CATALOG NUMBER: LD4D80BD010-EU4DR6570959050-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6994.7
2.5°	7024.6
5°	6973.9
7.5°	7079.2
10°	7136.9
12.5°	7123.0
15°	7011.6
17.5°	6739.3
20°	6280.1
22.5°	5739.3
25°	5160.8
27.5°	4507.8
30°	3775.2
32.5°	3111.2
35°	2522.8
37.5°	1941.3
40°	1392.6
42.5°	909.5
45°	521.8
47.5°	276.3
50°	172.0
52.5°	119.3
55°	85.5
57.5°	61.6
60°	42.7
62.5°	27.8
65°	19.9
67.5°	17.9
70°	16.9
72.5°	12.9
75°	9.9
77.5°	8.9
80°	7.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)