

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755101

Luminaire Tested: LD4D85BD010-EU4DR6570959024-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959024-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6084.7 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P755101

CATALOG NUMBER: LD4D85BD010-EU4DR6570959024-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P755101

CATALOG NUMBER: LD4D85BD010-EU4DR6570959024-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322670
5°	321856
10°	321581
15°	311668
20°	283731
25°	247256
30°	205648
35°	162944
40°	117609
45°	74303
50°	38725
55°	20589
60°	10816
65°	5942
70°	2493
75°	2753
80°	1917
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 74303 cd/sqm



TEST NUMBER: P755101

CATALOG NUMBER: LD4D85BD010-EU4DR6570959024-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	522.5	8.6
10°-20°	1430.7	23.5
20°-30°	1748.8	28.7
30°-40°	1418.9	23.3
40°-50°	707.1	11.6
50°-60°	197.2	3.2
60°-70°	44.8	0.7
70°-80°	11.7	0.2
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3702.0	60.8
0°-40°	5121.0	84.2
0°-60°	6025.3	99.0
0°-90°	6084.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6084.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5525	
5°	5490	522
15°	5155	1431
25°	3837	1749
35°	2285	1419
45°	900	707
55°	202	197
65°	43	45
75°	12	12
85°	2	3
90°	0	



TEST NUMBER: P755101

CATALOG NUMBER: LD4D85BD010-EU4DR6570959024-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5524.8
2.5°	5520.7
5°	5489.9
7.5°	5472.0
10°	5422.5
12.5°	5321.8
15°	5154.6
17.5°	4893.1
20°	4565.1
22.5°	4211.2
25°	3836.9
27.5°	3436.6
30°	3049.4
32.5°	2667.0
35°	2285.4
37.5°	1904.6
40°	1542.6
42.5°	1203.2
45°	899.6
47.5°	626.8
50°	426.2
52.5°	293.9
55°	202.2
57.5°	136.4
60°	92.6
62.5°	64.1
65°	43.0
67.5°	21.9
70°	14.6
72.5°	13.8
75°	12.2
77.5°	8.1
80°	5.7
82.5°	4.1
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)