

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754798

Luminaire Tested: LD4D85BD010-EU4DR4570959027-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR4570959027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7622.4 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P754798
CATALOG NUMBER: LD4D85BD010-EU4DR4570959027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754798

CATALOG NUMBER: LD4D85BD010-EU4DR4570959027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66	66
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1472037
5°	1430126
10°	1368245
15°	1252229
20°	993447
25°	620224
30°	341852
35°	153497
40°	60461
45°	28493
50°	13513
55°	7067
60°	3474
65°	827
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28493 cd/sqm



TEST NUMBER: P754798

CATALOG NUMBER: LD4D85BD010-EU4DR4570959027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1225.2	16.1
10°-20°	3015.3	39.6
20°-30°	2387.8	31.3
30°-40°	795.2	10.4
40°-50°	157.8	2.1
50°-60°	35.9	0.5
60°-70°	5.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6628.2	87.0
0°-40°	7423.4	97.4
0°-60°	7617.1	99.9
0°-90°	7622.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7622.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13473	
5°	13039	###
15°	11070	3015
25°	5145	2388
35°	1151	795
45°	184	158
55°	37	36
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754798

CATALOG NUMBER: LD4D85BD010-EU4DR4570959027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	13472.7
2.5°	13384.7
5°	13039.3
7.5°	12754.2
10°	12332.5
12.5°	11770.8
15°	11070.4
17.5°	10017.1
20°	8544.1
22.5°	6789.3
25°	5144.7
27.5°	3767.1
30°	2709.6
32.5°	1842.8
35°	1150.8
37.5°	682.4
40°	423.9
42.5°	278.7
45°	184.4
47.5°	118.7
50°	79.5
52.5°	53.0
55°	37.1
57.5°	24.4
60°	15.9
62.5°	8.5
65°	3.2
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)