

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754952

Luminaire Tested: LD4D85BD010-EU4DR5570959027-4LBDP1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754952  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR5570959027-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8041.8 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P754952

CATALOG NUMBER: LD4D85BD010-EU4DR5570959027-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P754952  
 CATALOG NUMBER: LD4D85BD010-EU4DR5570959027-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87				
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75				
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70				
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65				
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61				
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57				
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54				
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50				

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	985259
5°	946127
10°	942566
15°	915485
20°	820863
25°	678404
30°	512451
35°	371564
40°	237792
45°	108611
50°	35526
55°	15334
60°	6599
65°	879
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 108611 cd/sqm



TEST NUMBER: P754952

CATALOG NUMBER: LD4D85BD010-EU4DR5570959027-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	820.9	10.2
10°-20°	2240.3	27.9
20°-30°	2553.0	31.7
30°-40°	1738.0	21.6
40°-50°	598.9	7.4
50°-60°	82.8	1.0
60°-70°	8.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5614.1	69.8
0°-40°	7352.0	91.4
0°-60°	8033.7	99.9
0°-90°	8041.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8041.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9018	
5°	8626	821
15°	8093	2240
25°	5627	2553
35°	2786	1738
45°	703	599
55°	80	83
65°	3	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754952

CATALOG NUMBER: LD4D85BD010-EU4DR5570959027-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9017.5
2.5°	8810.8
5°	8626.4
7.5°	8535.9
10°	8495.7
12.5°	8361.6
15°	8093.4
17.5°	7667.7
20°	7059.8
22.5°	6358.1
25°	5627.3
27.5°	4866.3
30°	4061.8
32.5°	3380.2
35°	2785.7
37.5°	2220.3
40°	1667.2
42.5°	1155.4
45°	702.9
47.5°	378.8
50°	209.0
52.5°	124.0
55°	80.5
57.5°	51.4
60°	30.2
62.5°	13.4
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)