

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741145

Luminaire Tested: LD4D08D010-EU4DR300210IC9040-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P741145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR300210IC9040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 792.4 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741145
CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P741145

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	195033	195033	195033
5°	189431	189208	189439
10°	164076	162918	164037
15°	107050	106472	105941
20°	53231	55227	53158
25°	26815	30235	26266
30°	10739	11702	9351
35°	4980	4766	3999
40°	2148	2388	2028
45°	1515	1884	1537
50°	524	1369	548
55°	294	560	307
60°	214	245	214
65°	127	127	127
70°	90	45	90
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 1884 cd/sqm



TEST NUMBER: P741145

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.1	28.3
10°-20°	360.8	45.5
20°-30°	155.9	19.7
30°-40°	35.5	4.5
40°-50°	12.2	1.5
50°-60°	3.0	0.4
60°-70°	0.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.8	93.5
0°-40°	776.4	98.0
0°-60°	791.5	99.9
0°-90°	792.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	792.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2548	2548	2548	2548	2548	
5°	2465	2463	2462	2468	2466	224
15°	1351	1335	1344	1339	1337	362
25°	318	330	358	321	311	152
35°	53	54	51	51	43	36
45°	14	17	17	17	14	10
55°	2	2	4	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P741145

CATALOG NUMBER: LD4D08D010-EU4DR300210IC9040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2548.0	2548.0	2548.0	2548.0	2548.0
2.5°	2531.1	2529.3	2530.3	2531.6	2532.0
5°	2465.4	2463.0	2462.5	2467.6	2465.5
7.5°	2332.9	2329.5	2324.4	2336.0	2346.9
10°	2111.0	2107.3	2096.1	2101.6	2110.5
12.5°	1783.4	1771.2	1771.0	1788.5	1786.1
15°	1350.9	1334.6	1343.6	1339.3	1336.9
17.5°	908.5	902.2	914.2	910.6	894.9
20°	653.5	655.1	678.0	666.5	652.6
22.5°	476.9	482.8	509.9	480.2	469.4
25°	317.5	329.5	358.0	321.1	311.0
27.5°	195.3	200.8	229.7	192.8	187.2
30°	121.5	118.7	132.4	113.6	105.8
32.5°	79.7	76.2	80.6	72.3	66.1
35°	53.3	54.4	51.0	50.6	42.8
37.5°	33.3	38.3	33.8	36.0	27.5
40°	21.5	27.8	23.9	26.4	20.3
42.5°	17.6	21.4	19.7	20.9	18.0
45°	14.0	17.4	17.4	17.4	14.2
47.5°	7.7	11.6	14.9	11.9	8.3
50°	4.4	5.9	11.5	6.1	4.6
52.5°	3.0	3.4	7.9	3.5	3.2
55°	2.2	2.3	4.2	2.5	2.3
57.5°	1.8	1.9	2.2	1.9	1.8
60°	1.4	1.4	1.6	1.5	1.4
62.5°	1.0	1.0	1.1	1.0	1.0
65°	0.7	0.7	0.7	0.7	0.7
67.5°	0.4	0.5	0.5	0.5	0.5
70°	0.4	0.2	0.2	0.2	0.4
72.5°	0.2	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)