

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755185

Luminaire Tested: LD4D85BD010-EU4DR7070959027-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR7070959027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4618.7 lumens
Efficiency: N/A
Efficacy: 52.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755185
CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P755185

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	567358
5°	550496
10°	535160
15°	528134
20°	493171
25°	370492
30°	261903
35°	92768
40°	48779
45°	51964
50°	53799
55°	54823
60°	55155
65°	53982
70°	50953
75°	47196
80°	41905
85°	33973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 55169 cd/sqm



TEST NUMBER: P755185

CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	473.4	10.3
10°-20°	1298.6	28.1
20°-30°	1430.2	31.0
30°-40°	546.4	11.8
40°-50°	258.0	5.6
50°-60°	256.5	5.6
60°-70°	205.4	4.4
70°-80°	118.0	2.6
80°-90°	32.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3202.2	69.3
0°-40°	3748.6	81.2
0°-60°	4263.2	92.3
0°-90°	4618.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4618.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5193	
5°	5019	473
15°	4669	1299
25°	3073	1430
35°	696	546
45°	336	258
55°	288	257
65°	209	205
75°	112	118
85°	27	32
90°	0	



TEST NUMBER: P755185
CATALOG NUMBER: LD4D85BD010-EU4DR7070959027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5192.7
2.5°	5138.5
5°	5019.2
7.5°	4919.8
10°	4823.6
12.5°	4742.2
15°	4669.0
17.5°	4492.2
20°	4241.5
22.5°	3700.5
25°	3073.2
27.5°	2675.3
30°	2075.9
32.5°	1340.9
35°	695.5
37.5°	375.7
40°	342.0
42.5°	339.5
45°	336.3
47.5°	328.9
50°	316.5
52.5°	302.6
55°	287.8
57.5°	271.3
60°	252.4
62.5°	231.0
65°	208.8
67.5°	184.2
70°	159.5
72.5°	134.8
75°	111.8
77.5°	88.0
80°	66.6
82.5°	46.9
85°	27.1
87.5°	10.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)