

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741763

Luminaire Tested: LD4D08D010-EU4DR700210IC9040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P741763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR700210IC9040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 818.6 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741763

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P741763

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100553
5°	97570
10°	94848
15°	93603
20°	87414
25°	65667
30°	46416
35°	16446
40°	8643
45°	9209
50°	9536
55°	9715
60°	9768
65°	9566
70°	9009
75°	8359
80°	7425
85°	6017

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 9781 cd/sqm



TEST NUMBER: P741763

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	10.3
10°-20°	230.2	28.1
20°-30°	253.5	31.0
30°-40°	96.9	11.8
40°-50°	45.7	5.6
50°-60°	45.5	5.6
60°-70°	36.4	4.4
70°-80°	20.9	2.6
80°-90°	5.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.6	69.3
0°-40°	664.4	81.2
0°-60°	755.6	92.3
0°-90°	818.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	818.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	920	
5°	890	84
15°	828	230
25°	545	253
35°	123	97
45°	60	46
55°	51	45
65°	37	36
75°	20	21
85°	5	6
90°	0	



TEST NUMBER: P741763

CATALOG NUMBER: LD4D08D010-EU4DR700210IC9040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	920.3
2.5°	910.7
5°	889.6
7.5°	872.0
10°	854.9
12.5°	840.5
15°	827.5
17.5°	796.2
20°	751.8
22.5°	655.9
25°	544.7
27.5°	474.2
30°	367.9
32.5°	237.7
35°	123.3
37.5°	66.6
40°	60.6
42.5°	60.2
45°	59.6
47.5°	58.3
50°	56.1
52.5°	53.6
55°	51.0
57.5°	48.1
60°	44.7
62.5°	41.0
65°	37.0
67.5°	32.7
70°	28.2
72.5°	23.9
75°	19.8
77.5°	15.6
80°	11.8
82.5°	8.3
85°	4.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)