

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755042

Luminaire Tested: LD4D85BD010-EU4DR6070959030-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755042  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR6070959030-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6398.2 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P755042  
CATALOG NUMBER: LD4D85BD010-EU4DR6070959030-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P755042

CATALOG NUMBER: LD4D85BD010-EU4DR6070959030-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	830229
5°	850642
10°	860921
15°	820141
20°	723113
25°	584877
30°	395623
35°	198247
40°	32163
45°	31475
50°	32109
55°	32593
60°	33499
65°	34256
70°	35076
75°	35503
80°	34229
85°	28457

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 35503 cd/sqm



TEST NUMBER: P755042

CATALOG NUMBER: LD4D85BD010-EU4DR6070959030-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	741.3	11.6
10°-20°	2005.5	31.3
20°-30°	2157.8	33.7
30°-40°	938.0	14.7
40°-50°	157.5	2.5
50°-60°	153.2	2.4
60°-70°	131.0	2.0
70°-80°	87.7	1.4
80°-90°	26.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4904.6	76.7
0°-40°	5842.5	91.3
0°-60°	6153.3	96.2
0°-90°	6398.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6398.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7599	
5°	7756	741
15°	7250	2006
25°	4852	2158
35°	1486	938
45°	204	158
55°	171	153
65°	132	131
75°	84	88
85°	23	26
90°	0	



TEST NUMBER: P755042

CATALOG NUMBER: LD4D85BD010-EU4DR6070959030-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7598.6
2.5°	7812.2
5°	7755.8
7.5°	7773.6
10°	7759.8
12.5°	7599.6
15°	7250.5
17.5°	6781.8
20°	6219.1
22.5°	5616.9
25°	4851.5
27.5°	3880.4
30°	3135.8
32.5°	2416.8
35°	1486.3
37.5°	635.9
40°	225.5
42.5°	207.7
45°	203.7
47.5°	196.8
50°	188.9
52.5°	180.0
55°	171.1
57.5°	162.2
60°	153.3
62.5°	143.4
65°	132.5
67.5°	121.6
70°	109.8
72.5°	96.9
75°	84.1
77.5°	69.2
80°	54.4
82.5°	38.6
85°	22.7
87.5°	7.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)