

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741700

Luminaire Tested: LD4D08D010-EU4DR650210IC9050-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P741700
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D08D010-EU4DR650210IC9050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 605.8 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 8.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741700
CATALOG NUMBER: LD4D08D010-EU4DR650210IC9050-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P741700
 CATALOG NUMBER: LD4D08D010-EU4DR650210IC9050-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																												
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																												
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																												
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																												
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																												
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																												
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																												
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																												
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																												
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65185
5°	65237
10°	67522
15°	67643
20°	62276
25°	53057
30°	40612
35°	28691
40°	16944
45°	6876
50°	2499
55°	1391
60°	809
65°	440
70°	447
75°	380
80°	378
85°	251

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6876 cd/sqm



TEST NUMBER: P741700

CATALOG NUMBER: LD4D08D010-EU4DR650210IC9050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	9.5
10°-20°	165.7	27.3
20°-30°	198.8	32.8
30°-40°	133.6	22.1
40°-50°	40.0	6.6
50°-60°	7.1	1.2
60°-70°	2.0	0.3
70°-80°	1.0	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	421.9	69.6
0°-40°	555.5	91.7
0°-60°	602.6	99.5
0°-90°	605.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	597	
5°	595	57
15°	598	166
25°	440	199
35°	215	134
45°	44	40
55°	7	7
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P741700

CATALOG NUMBER: LD4D08D010-EU4DR650210IC9050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	596.6
2.5°	599.1
5°	594.8
7.5°	603.7
10°	608.6
12.5°	607.4
15°	598.0
17.5°	574.7
20°	535.6
22.5°	489.5
25°	440.1
27.5°	384.4
30°	321.9
32.5°	265.3
35°	215.1
37.5°	165.6
40°	118.8
42.5°	77.6
45°	44.5
47.5°	23.5
50°	14.7
52.5°	10.2
55°	7.3
57.5°	5.3
60°	3.7
62.5°	2.3
65°	1.7
67.5°	1.5
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)