

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755137

Luminaire Tested: LD4D85BD010-EU4DR6570959035-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P755137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959035-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7011.4 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P755137
CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P755137

CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371811
5°	370874
10°	370554
15°	359133
20°	326945
25°	284909
30°	236967
35°	187763
40°	135518
45°	85619
50°	44621
55°	23715
60°	12452
65°	6854
70°	2869
75°	3159
80°	2186
85°	1876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 85619 cd/sqm



TEST NUMBER: P755137

CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	602.0	8.6
10°-20°	1648.6	23.5
20°-30°	2015.2	28.7
30°-40°	1635.1	23.3
40°-50°	814.8	11.6
50°-60°	227.3	3.2
60°-70°	51.6	0.7
70°-80°	13.4	0.2
80°-90°	3.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4265.8	60.8
0°-40°	5900.9	84.2
0°-60°	6942.9	99.0
0°-90°	7011.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7011.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6366	
5°	6326	602
15°	5940	1649
25°	4421	2015
35°	2634	1635
45°	1037	815
55°	233	227
65°	50	52
75°	14	13
85°	3	3
90°	0	



TEST NUMBER: P755137

CATALOG NUMBER: LD4D85BD010-EU4DR6570959035-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6366.2
2.5°	6361.5
5°	6326.0
7.5°	6305.4
10°	6248.3
12.5°	6132.3
15°	5939.6
17.5°	5638.4
20°	5260.4
22.5°	4852.5
25°	4421.2
27.5°	3960.0
30°	3513.8
32.5°	3073.2
35°	2633.5
37.5°	2194.7
40°	1777.5
42.5°	1386.4
45°	1036.6
47.5°	722.2
50°	491.1
52.5°	338.7
55°	232.9
57.5°	157.2
60°	106.6
62.5°	73.9
65°	49.6
67.5°	25.3
70°	16.8
72.5°	15.9
75°	14.0
77.5°	9.4
80°	6.5
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)