

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755211

Luminaire Tested: LD4D85BD010-EU4DR7070959035-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755211  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR7070959035-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4808.4 lumens  
Efficiency: N/A  
Efficacy: 54.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P755211  
CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P755211  
 CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	590664
5°	573112
10°	557139
15°	549830
20°	513426
25°	385707
30°	272664
35°	96582
40°	50790
45°	54097
50°	56008
55°	57071
60°	57427
65°	56205
70°	53030
75°	49138
80°	43604
85°	35352

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 57447 cd/sqm



TEST NUMBER: P755211

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	492.9	10.3
10°-20°	1351.9	28.1
20°-30°	1488.9	31.0
30°-40°	568.9	11.8
40°-50°	268.6	5.6
50°-60°	267.1	5.6
60°-70°	213.8	4.4
70°-80°	122.9	2.6
80°-90°	33.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3333.7	69.3
0°-40°	3902.6	81.2
0°-60°	4438.3	92.3
0°-90°	4808.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4808.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5406	
5°	5225	493
15°	4861	1352
25°	3199	1489
35°	724	569
45°	350	269
55°	300	267
65°	217	214
75°	116	123
85°	28	33
90°	0	



TEST NUMBER: P755211

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5406.0
2.5°	5349.5
5°	5225.4
7.5°	5121.8
10°	5021.7
12.5°	4936.9
15°	4860.8
17.5°	4676.7
20°	4415.7
22.5°	3852.5
25°	3199.4
27.5°	2785.2
30°	2161.2
32.5°	1396.0
35°	724.1
37.5°	391.2
40°	356.1
42.5°	353.5
45°	350.1
47.5°	342.4
50°	329.5
52.5°	315.0
55°	299.6
57.5°	282.5
60°	262.8
62.5°	240.5
65°	217.4
67.5°	191.7
70°	166.0
72.5°	140.4
75°	116.4
77.5°	91.6
80°	69.3
82.5°	48.8
85°	28.2
87.5°	11.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)