

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754408

Luminaire Tested: LD4D80BD010-EU4DR7070959027-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P754408  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D80BD010-EU4DR7070959027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5824.4 lumens  
Efficiency: N/A  
Efficacy: 73.8 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 78.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P754408

CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P754408  
 CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	715483
5°	694219
10°	674864
15°	666010
20°	621920
25°	467214
30°	330283
35°	116990
40°	61516
45°	65516
50°	67856
55°	69129
60°	69555
65°	68072
70°	64243
75°	59523
80°	52853
85°	42874

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 69567 cd/sqm



TEST NUMBER: P754408

CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	597.0	10.3
10°-20°	1637.6	28.1
20°-30°	1803.6	31.0
30°-40°	689.1	11.8
40°-50°	325.4	5.6
50°-60°	323.5	5.6
60°-70°	259.0	4.4
70°-80°	148.8	2.6
80°-90°	40.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4038.2	69.3
0°-40°	4727.3	81.2
0°-60°	5376.1	92.3
0°-90°	5824.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5824.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6548	
5°	6330	597
15°	5888	1638
25°	3876	1804
35°	877	689
45°	424	325
55°	363	323
65°	263	259
75°	141	149
85°	34	40
90°	0	



TEST NUMBER: P754408  
CATALOG NUMBER: LD4D80BD010-EU4DR7070959027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6548.4
2.5°	6479.9
5°	6329.6
7.5°	6204.1
10°	6082.8
12.5°	5980.2
15°	5887.9
17.5°	5665.0
20°	5348.8
22.5°	4666.6
25°	3875.5
27.5°	3373.7
30°	2617.9
32.5°	1691.0
35°	877.1
37.5°	473.8
40°	431.3
42.5°	428.2
45°	424.0
47.5°	414.7
50°	399.2
52.5°	381.5
55°	362.9
57.5°	342.1
60°	318.3
62.5°	291.3
65°	263.3
67.5°	232.2
70°	201.1
72.5°	170.0
75°	141.0
77.5°	110.9
80°	84.0
82.5°	59.1
85°	34.2
87.5°	13.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)