

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754265

Luminaire Tested: LD4D80BD010-EU4DR6070959030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6070959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6911.7 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P754265
CATALOG NUMBER: LD4D80BD010-EU4DR6070959030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754265

CATALOG NUMBER: LD4D80BD010-EU4DR6070959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	896867
5°	918927
10°	930018
15°	885974
20°	781156
25°	631821
30°	427366
35°	214159
40°	34745
45°	34009
50°	34676
55°	35203
60°	36187
65°	36996
70°	37888
75°	38331
80°	36997
85°	30839

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 38331 cd/sqm



TEST NUMBER: P754265

CATALOG NUMBER: LD4D80BD010-EU4DR6070959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	800.8	11.6
10°-20°	2166.5	31.3
20°-30°	2331.0	33.7
30°-40°	1013.2	14.7
40°-50°	170.2	2.5
50°-60°	165.5	2.4
60°-70°	141.5	2.0
70°-80°	94.7	1.4
80°-90°	28.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5298.2	76.7
0°-40°	6311.5	91.3
0°-60°	6647.1	96.2
0°-90°	6911.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6911.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8208	
5°	8378	801
15°	7832	2167
25°	5241	2331
35°	1606	1013
45°	220	170
55°	185	165
65°	143	142
75°	91	95
85°	25	28
90°	0	



TEST NUMBER: P754265

CATALOG NUMBER: LD4D80BD010-EU4DR6070959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8208.5
2.5°	8439.2
5°	8378.4
7.5°	8397.6
10°	8382.6
12.5°	8209.6
15°	7832.5
17.5°	7326.1
20°	6718.3
22.5°	6067.7
25°	5240.9
27.5°	4191.8
30°	3387.4
32.5°	2610.8
35°	1605.6
37.5°	686.9
40°	243.6
42.5°	224.3
45°	220.1
47.5°	212.6
50°	204.0
52.5°	194.4
55°	184.8
57.5°	175.2
60°	165.6
62.5°	154.9
65°	143.1
67.5°	131.4
70°	118.6
72.5°	104.7
75°	90.8
77.5°	74.8
80°	58.8
82.5°	41.7
85°	24.6
87.5°	8.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)