

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754276

Luminaire Tested: LD4D80BD010-EU4DR6070959035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P754276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR6070959035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7712.4 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P754276

CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P754276

CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1000774
5°	1025392
10°	1037769
15°	988614
20°	871663
25°	705023
30°	476885
35°	238969
40°	38767
45°	37950
50°	38704
55°	39279
60°	40383
65°	41288
70°	42264
75°	42764
80°	41276
85°	34349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 42764 cd/sqm



TEST NUMBER: P754276

CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	893.5	11.6
10°-20°	2417.5	31.3
20°-30°	2601.1	33.7
30°-40°	1130.6	14.7
40°-50°	189.9	2.5
50°-60°	184.6	2.4
60°-70°	157.9	2.0
70°-80°	105.7	1.4
80°-90°	31.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5912.1	76.7
0°-40°	7042.7	91.3
0°-60°	7417.3	96.2
0°-90°	7712.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7712.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9160	
5°	9349	894
15°	8740	2418
25°	5848	2601
35°	1792	1131
45°	246	190
55°	206	185
65°	160	158
75°	101	106
85°	27	32
90°	0	



TEST NUMBER: P754276

CATALOG NUMBER: LD4D80BD010-EU4DR6070959035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9159.5
2.5°	9417.0
5°	9349.1
7.5°	9370.5
10°	9353.8
12.5°	9160.7
15°	8739.9
17.5°	8174.9
20°	7496.7
22.5°	6770.7
25°	5848.1
27.5°	4677.5
30°	3779.9
32.5°	2913.3
35°	1791.6
37.5°	766.5
40°	271.8
42.5°	250.3
45°	245.6
47.5°	237.2
50°	227.7
52.5°	216.9
55°	206.2
57.5°	195.5
60°	184.8
62.5°	172.8
65°	159.7
67.5°	146.6
70°	132.3
72.5°	116.8
75°	101.3
77.5°	83.4
80°	65.6
82.5°	46.5
85°	27.4
87.5°	9.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)