

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753745

Luminaire Tested: LD4D80BD010-EU4DR2570959040-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR2570959040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6369.7 lumens
Efficiency: N/A
Efficacy: 80.7 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P753745
CATALOG NUMBER: LD4D80BD010-EU4DR2570959040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P753745

CATALOG NUMBER: LD4D80BD010-EU4DR2570959040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2639631
5°	2458490
10°	1753706
15°	1032865
20°	642663
25°	352698
30°	161300
35°	61089
40°	27670
45°	16626
50°	6901
55°	4457
60°	3103
65°	2094
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16626 cd/sqm



TEST NUMBER: P753745

CATALOG NUMBER: LD4D80BD010-EU4DR2570959040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1926.4	30.2
10°-20°	2609.2	41.0
20°-30°	1380.8	21.7
30°-40°	340.9	5.4
40°-50°	83.2	1.3
50°-60°	21.9	0.3
60°-70°	7.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5916.4	92.9
0°-40°	6257.2	98.2
0°-60°	6362.3	99.9
0°-90°	6369.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6369.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24159	
5°	22416	###
15°	9131	2609
25°	2926	1381
35°	458	341
45°	108	83
55°	23	22
65°	8	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753745
CATALOG NUMBER: LD4D80BD010-EU4DR2570959040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	24159.0
2.5°	23762.0
5°	22415.5
7.5°	19710.3
10°	15806.8
12.5°	11949.0
15°	9131.1
17.5°	7116.4
20°	5527.2
22.5°	4145.1
25°	2925.6
27.5°	1961.9
30°	1278.5
32.5°	777.8
35°	458.0
37.5°	280.3
40°	194.0
42.5°	148.3
45°	107.6
47.5°	65.0
50°	40.6
52.5°	29.4
55°	23.4
57.5°	18.3
60°	14.2
62.5°	11.2
65°	8.1
67.5°	3.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)